

## Digital ABS Inside Point Jaw Caliper

Item number: 573-746-20

### Images



Dust- and Water-Protected

www.tuv.com  
ID 0000045042

# ABSOLUTE®

# IP67

### Description


A Mitutoyo waterproof digital caliper suitable for use in the presence of coolant or cutting oil. Equipped with knife-edge jaws for inside measurement only. ABSOLUTE System scale for error free, high-speed measurement. SPC data output.

### Features

<b>Range:</b>	0,804 - 6 "
<b>Delivered:</b>	In a box with SR44 battery
<b>Thumb roller:</b>	Yes
<b>Max. Permissible Error S MPE:</b>	±0,0015"
<b>Max. response speed:</b>	Unlimited
<b>ORIGIN (ABS-Zero):</b>	Yes
<b>OFFSET:</b>	0.4"
<b>Auto Power OFF after 20 min. non use:</b>	Yes

<b>Low voltage alarm:</b>	Yes
<b>Data output:</b>	Yes
<b>Battery life:</b>	Approx. 5 years under normal use
<b>Mass:</b>	157 g

## Dimensions



## Accessories

### Optional accessories:

Promotion!

Mitutoyo

MiCAT

the standard in world  
metrology software  
MeasurLink

### USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available Online)

Art No. 06AGR543

Promo price: **268.00 €\***

Suggested retail price: ~~340.00 €\*~~



### Digimatic Cable with Data Button IP Type

1 m, Caliper Type

Art No. 05CZA624

Suggested retail price: 100.00 €\*



### Digimatic Cable with Data Button IP Type

2 m, Caliper Type

Art No. 05CZA625

Suggested retail price: 107.00 €\*

Promotion!



### USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data  
Button IP Caliper Type  
Art No. 06AFM380A

Promo price: **111.00 €\***

Suggested retail price: ~~141.00 €\*~~

Promotion!



### U-WAVE fit, IP67 Type

Wireless Transmitter for Caliper  
Art No. 264-620

Promo price: **129.00 €\***

Suggested retail price: ~~185.00 €\*~~

Promotion!



### U-WAVE fit, Buzzer Type

Wireless Transmitter for Caliper  
Art No. 264-621

Promo price: **129.00 €\***

Suggested retail price: ~~185.00 €\*~~

Promotion!



### U-WAVE fit Bluetooth, IP67 Type

Wireless Transmitter for Caliper  
Art No. 264-624

Promo price: **129.00 €\***

Suggested retail price: ~~185.00 €\*~~

Promotion!



### U-WAVE fit Bluetooth, Buzzer Type

Wireless Transmitter for Caliper  
Art No. 264-625

Promo price: **129.00 €\***

Suggested retail price: ~~185.00 €\*~~

Promotion!



## Connection Unit for IP Caliper, Micrometer

with Data Button for U-WAVE fit, U-WAVE fit Bluetooth

Art No. 02AZF310

Promo price: **76.00 €\***

Suggested retail price: ~~110.00 €\*~~




## Depth Base Attachment for Caliper

75mm width for 100, 150, 200mm Range

Art No. 050083-10

Suggested retail price: **60.00 €\***



## Depth Base Attachment for Caliper

100mm width for 100, 150, 200mm Range

Art No. 050084-10

Suggested retail price: **67.00 €\***

### Spare parts

Consumable spares:



## Battery SR44 1,5 V

Art No. 938882

Suggested retail price: **7.00 €\***