

Digital ABS Neck Point Jaw Caliper

Item number: 573-752-20

Images



Dust- and Water-Protected

www.tuv.com
ID 000045042

ABSOLUTE®

IP67

Description

A Mitutoyo waterproof digital caliper suitable for use in the presence of coolant or cutting oil. Equipped with special pointed jaws for outside measurement only. ABSOLUTE System scale for error free, high-speed measurement. SPC data output.


Features

Range:	0 - 6 "
Delivered:	In a box with SR44 battery
Thumb roller:	Yes
Max. Permissible Error E MPE:	$\pm 0.0015''/\pm 0.03$ mm
Max. response speed:	Unlimited
ORIGIN (ABS-Zero):	Yes
Auto Power OFF after 20 min. non use:	Yes
Low voltage alarm:	Yes
Data output:	Yes

Resolution: 0.0005 in/0.01 mm

Mass: 157 g

Dimensions



Accessories

Optional accessories:

Promotion!

Mitutoyo

MiCAT
the standard in world metrology software
MeasurLink

USB-ITPAK

USB-ITPAK Vers. 3.0
USB Dongle + Manual (Software available Online)
Art No. 06AGR543
Promo price: 268.00 €*
Suggested retail price: ~~340.00 €*~~



Digimatic Cable with Data Button IP Type

1 m, Caliper Type
Art No. 05CZA624
Suggested retail price: 100.00 €*



Digimatic Cable with Data Button IP Type

2 m, Caliper Type
Art No. 05CZA625
Suggested retail price: 107.00 €*

Promotion!



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data
Button IP Caliper Type
Art No. 06AFM380A

Promo price: **111.00 €***

Suggested retail price: ~~141.00 €*~~

Promotion!



U-WAVE fit, IP67 Type

Wireless Transmitter for Caliper
Art No. 264-620

Promo price: **129.00 €***

Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit, Buzzer Type

Wireless Transmitter for Caliper
Art No. 264-621

Promo price: **129.00 €***

Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit Bluetooth, IP67 Type

Wireless Transmitter for Caliper
Art No. 264-624

Promo price: **129.00 €***

Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit Bluetooth, Buzzer Type

Wireless Transmitter for Caliper
Art No. 264-625

Promo price: **129.00 €***

Suggested retail price: ~~185.00 €*~~

Promotion!



Connection Unit for IP Caliper, Micrometer

with Data Button for U-WAVE fit, U-WAVE fit Bluetooth

Art No. 02AZF310

Promo price: **76.00 €***

Suggested retail price: ~~110.00 €*~~



Depth Base Attachment for Caliper

75mm width for 100, 150, 200mm Range

Art No. 050083-10

Suggested retail price: **60.00 €***



Depth Base Attachment for Caliper

100mm width for 100, 150, 200mm Range

Art No. 050084-10

Suggested retail price: **67.00 €***

Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: **7.00 €***