



Digital ABS Caliper Nib Style/Std. Jaws

Item number: 551-204-10

Images



ABSOLUTE®

Description

This is a Digimatic caliper with nib-style and standard jaws.

It offers you the following benefits:

- Knife-shaped measuring surfaces allow you to take outside measurements.
- Rounded measuring surfaces enable you to measure inside dimensions.
- ABSOLUTE System delivers reliable measurements.

Features


Model:	CDN-50C
Digital/Analog:	Digital
Inch-Metric:	Metric
Range:	0 - 500 mm
Inside measuring from:	20.1 mm
Delivered:	In a box with SR44 battery
Max. Permissible Error E MPE:	±0,06 mm
Max. Permissible Error S MPE:	±0,06 mm
Digital step:	0,01 mm
Max. response speed:	Unlimited
Display:	LCD, character height 9 mm (200 mm) 11 mm (300 mm) 10 mm (>300 mm)
Battery life:	Approx. 5 years, 3,5 years (>300 mm)
ORIGIN (ABS-Zero):	Yes
ON/OFF:	Yes

Low voltage alarm: Yes

Data output: Yes

Mass: 1060 g

Dimensions



b: 56 mm

c: 44.9 mm

d: 150 mm

g: 10 mm

s: 18 mm

h: 25 mm

t: 6 mm

R: 10 mm

Accessories

Optional accessories:

Mitutoyo

MiCAT
the standard in world
metrology software
measurLink

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available Online)

Art No. 06AGR543

Suggested retail price: 340.00 €*

USB-ITPAK

Digimatic Cable, Straight, Data Button,

1m

Art No. 959149

Suggested retail price: 48.00 €*

Digimatic Cable, Straight, Data Button

2m

Art No. 959150

Suggested retail price: 57.00 €*



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, Straight,
with Data Button
Art No. 06AFM380C
Suggested retail price: 124.00 €*



U-WAVE-T, Buzzer Type

Wireless Transmitter
Art No. 02AZD880G
Suggested retail price: 187.00 €*



U-WAVE-T, IP67 Type

Wireless Transmitter
Art No. 02AZD730G
Suggested retail price: 187.00 €*



Connection Cable C for U- WAVE

Straight, with Data Button
Art No. 02AZD790C
Suggested retail price: 105.00 €*



Data Hold Unit

for Digital Caliper
Art No. 959143
Suggested retail price: 39.50 €*

Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €*
