

## Digital ABS Carb. Fibre Caliper Ceramic

Item number: 552-155-10

### Images



Safety  
Dust- and  
Water-  
Protected

www.tuv.com  
ID 000022582

# ABSOLUTE®

# IP66

### Description

This is a lightweight standard model of Digimatic caliper with ceramic jaws.

It offers you the following benefits:

- Its ultra-lightweight design (with carbon fibre reinforced material) reduces total weight by up to 50%.
- It has excellent resistance against water and dust (IP66 protection level) enabling you to use it in machining situations that include splashing coolant fluid.
- Direct readout of inside measurements from the LCD (you can easily set the offset value by using the offset button).
- Preset function lets you set a desired starting point.

### Features

<b>Model:</b>	CFC-45GC
<b>DATA (output with cable) / HOLD (display value):</b>	Yes
<b>Delivered:</b>	In a box with SR44 battery
<b>Range:</b>	0 - 450 mm
<b>Inside measuring from:</b>	20.1 mm
<b>Max. Permissible Error E MPE:</b>	±0,04 mm
<b>Max. Permissible Error S MPE:</b>	±0,04 mm
<b>OFFSET:</b>	20 mm
<b>Max. response speed:</b>	Unlimited
<b>ORIGIN (ABS-Zero):</b>	Yes
<b>OFFSET:</b>	20 mm
<b>Auto Power OFF after 20 min. non use:</b>	Yes

<b>Low voltage alarm:</b>	Yes
<b>Data output:</b>	Yes
<b>Battery life:</b>	Approx. 5000 hours
<b>Mass:</b>	715 g

## Dimensions

## Accessories

### Optional accessories:

Promotion!

Mitutoyo

MiCAT

the standard in world metrology software

MeasurLink

### USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available Online)

Art No. 06AGR543

**Promo price: 259.00 €\***

Suggested retail price: ~~340.00 €\*~~





### Holders (Clamps) Series 552

2 pcs., 450 and 600mm Range  
 Art No. 914053  
 Suggested retail price: 209.00 €\*



### Center to Center Jaws Series 552

2 pcs., (≥10,1mm) Metric  
 Art No. 914055  
 Suggested retail price: 272.00 €\*



### Inside Groove Jaws Series 552

2 pcs., Metric  
 Art No. 914057  
 Suggested retail price: 312.00 €\*

**Spare parts**

Consumable spares:

---



**Battery SR44 1,5 V**

Art No. 938882

Suggested retail price: 10.00 €\*  

---