

Digital ABS Borematic (Internal) Set

Item number: 568-967-10

Images



ABSOLUTE[®]



Description

Mitutoyo Interchangeable-Head Bore Gauge Set 0,5-1"

Features

Model:	SBM-2"DFST
Inch-Metric:	Inch/Metric
Digital/Analog:	Digital
Range:	1 - 2 "
Digital step:	0,00005" / 0,001 mm
Individual ranges:	1-1.2" 1.2-1.6" 1.6-2"
Power supply:	1 battery SR-44
Battery life:	approx. 5000 hours
Display:	LCD, character height: 11 mm
Measuring face:	Titanium coated hardened steel taper: tungsten carbide
Measuring method:	3-point
Setting rings included:	Ø1.2" (177-289) Ø1.6" (177-291)
ABS / INC (INC ZERO):	Yes
ON/OFF:	Yes

Function lock:	Yes
DATA (output with cable) / HOLD (display value):	Yes
2 x PRESET:	Yes
GO/±NG judgement:	Yes
Delivered:	In a box with SR44 battery, spanner 04GAA858 (2 pcs.), setting rings (2 pcs.)
Data output:	Yes
Mass:	1750 g

Accessories

Optional accessories:



Digimatic Cable, Flat Straight Type

1 m
 Art No. 905338
 Suggested retail price: 37.00 €*



Digimatic Cable, Flat Straight Type

2 m
 Art No. 905409
 Suggested retail price: 44.00 €*

Promotion!



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, Flat Straight Type
 Art No. 06AFM380F
Promo price: 98.00 €*
 Suggested retail price: 124.00 €*

Promotion!



U-WAVE-T, IP67 Type

Wireless Transmitter

Art No. 02AZD730G

Promo price: **129.00 €***

Suggested retail price: ~~187.00 €*~~

Promotion!



U-WAVE-T, Buzzer Type

Wireless Transmitter

Art No. 02AZD880G

Promo price: **129.00 €***

Suggested retail price: ~~187.00 €*~~

Promotion!



Connection Cable F for U-WAVE

Straight, without Data Button

Art No. 02AZD790F

Promo price: **68.00 €***

Suggested retail price: ~~98.00 €*~~

Holtest, Borematic Extension 100mm

for 6-12mm Measuring Range

Art No. 952322

Suggested retail price: **128.00 €***



Holtest, Borematic Extension 150mm

for 12-20mm Measuring Range

Art No. 952621

Suggested retail price: **120.00 €***





Holtest, Borematic Extension 150mm

for 20-50mm Measuring Range
Art No. 952622
Suggested retail price: 136.00 €*



Holtest, Borematic Extension 150mm

for 50-300mm Measuring Range
Art No. 952623
Suggested retail price: 216.00 €*

Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882
Suggested retail price: 7.00 €*
