

Digital ABS AOS Depth Gauge

Item number: 571-202-30

Images



ABSOLUTE®

Description

This is a standard model Digital Depth Gauge.


It offers you the following benefits:

- ABSOLUTE System gives you reliable measurements.
- Its base and measuring faces are hardened and micro-lapped for robustness.
- Large character height makes measurements easy to read.

Features

Model:	VDS-20AX
Inch-Metric:	Metric
Digital/Analog:	Digital
Power supply:	1 battery SR-44
Range:	0 - 200 mm
Digital step:	0,01 mm
Max. Permissible Error E MPE:	±0,02 mm
Max. response speed:	Unlimited
Battery life:	Approx. 5 years
Display:	LCD, character height 9 mm (150/200/300 mm), 10 mm (>300 mm)
Base (W x T):	100 x 6 mm
ORIGIN (ABS-Zero):	Yes
ON/OFF:	Yes
Low voltage alarm:	Yes
Data output:	Yes
ABS / INC (INC ZERO):	Yes
Mass:	227 g
Delivered:	Including box, 1 SR-44 battery

Dimensions



L: 289 mm

Accessories

Optional accessories:

Promotion!

Mitutoyo

MiCAT

the standard in world
metrology software
MeasurLink®

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available
Online)

Art No. 06AGR543

Promo price: **268.00 €***

Suggested retail price: ~~340.00 €*~~

USB-ITPAK



Digimatic Cable, Straight, Data Button,

1 m

Art No. 959149

Suggested retail price: 48.00 €*



Digimatic Cable, Straight, Data Button

2 m

Art No. 959150

Suggested retail price: 57.00 €*

Promotion!



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, Straight,
with Data Button

Art No. 06AFM380C

Promo price: **98.00 €***

Suggested retail price: ~~124.00 €*~~

Promotion!



U-WAVE fit, IP67 Type

Wireless Transmitter for Caliper
Art No. 264-620

Promo price: **129.00 €***
Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit, Buzzer Type

Wireless Transmitter for Caliper
Art No. 264-621

Promo price: **129.00 €***
Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit Bluetooth, IP67 Type

Wireless Transmitter for Caliper
Art No. 264-624

Promo price: **129.00 €***
Suggested retail price: ~~185.00 €*~~

Promotion!



U-WAVE fit Bluetooth, Buzzer Type

Wireless Transmitter for Caliper
Art No. 264-625

Promo price: **129.00 €***
Suggested retail price: ~~185.00 €*~~

Promotion!



Connection Unit for Standard Caliper

with Data Button for U-WAVE fit, U-WAVE fit Bluetooth
Art No. 02AZF300

Promo price: **72.00 €***
Suggested retail price: ~~105.00 €*~~



Data Hold Unit

for Digital Caliper
Art No. 959143
Suggested retail price: 39.50 €*

Extension Base, Depth Gauge

180mm width for up to 300mm Range
Art No. 900370
Suggested retail price: 69.00 €*




Extension Base, Depth Gauge

260mm width for up to 300mm Range
Art No. 900371
Suggested retail price: 93.00 €*



Extension Base, Depth Gauge

320mm width for up to 300mm Range
Art No. 900372
Suggested retail price: 107.00 €*



Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €*
