

## Digital ABS Depth Gauge

Item number: 571-203-30

### Images



# ABSOLUTE®

### Description

This is a standard model Digital Depth Gauge.


It offers you the following benefits:

- ABSOLUTE System gives you reliable measurements.
- Its base and measuring faces are hardened and micro-lapped for robustness.
- Large character height makes measurements easy to read.

### Features

<b>Model:</b>	VDS-30AX
<b>Inch-Metric:</b>	Metric
<b>Digital/Analog:</b>	Digital
<b>Power supply:</b>	1 battery SR-44
<b>Range:</b>	0 - 300 mm
<b>Digital step:</b>	0,01 mm
<b>Max. Permissible Error E MPE:</b>	±0,03 mm
<b>Max. response speed:</b>	Unlimited
<b>Battery life:</b>	Approx. 5 years
<b>Display:</b>	LCD, character height 9 mm (150/200/300 mm), 10 mm (>300 mm)
<b>Base (W x T):</b>	100 x 6 mm
<b>ORIGIN (ABS-Zero):</b>	Yes
<b>ON/OFF:</b>	Yes
<b>Low voltage alarm:</b>	Yes
<b>Data output:</b>	Yes
<b>ABS / INC (INC ZERO):</b>	Yes
<b>Mass:</b>	310 g
<b>Delivered:</b>	In a box with SR44 battery

### Dimensions



L: 403 mm

## Accessories

### Optional accessories:

Promotion!

Mitutoyo

MiCAT

the standard in world  
metrology software  
MeasurLink®

### USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available  
Online)

Art No. 06AGR543

Promo price: **268.00 €\***

Suggested retail price: ~~340.00 €\*~~

USB-ITPAK



### Digimatic Cable, Straight, Data Button,

1 m

Art No. 959149

Suggested retail price: 48.00 €\*



### Digimatic Cable, Straight, Data Button

2 m

Art No. 959150

Suggested retail price: 57.00 €\*

Promotion!



### USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, Straight,  
with Data Button

Art No. 06AFM380C

Promo price: **98.00 €\***

Suggested retail price: ~~124.00 €\*~~

Promotion!



### U-WAVE fit, IP67 Type

Wireless Transmitter for Caliper  
Art No. 264-620

Promo price: **129.00 €\***

Suggested retail price: ~~185.00 €\*~~

Promotion!



### U-WAVE fit, Buzzer Type

Wireless Transmitter for Caliper  
Art No. 264-621

Promo price: **129.00 €\***

Suggested retail price: ~~185.00 €\*~~

Promotion!



### U-WAVE fit Bluetooth, IP67 Type

Wireless Transmitter for Caliper  
Art No. 264-624

Promo price: **129.00 €\***

Suggested retail price: ~~185.00 €\*~~

Promotion!



### U-WAVE fit Bluetooth, Buzzer Type

Wireless Transmitter for Caliper  
Art No. 264-625

Promo price: **129.00 €\***

Suggested retail price: ~~185.00 €\*~~

Promotion!



### Connection Unit for Standard Caliper

with Data Button for U-WAVE fit, U-WAVE fit Bluetooth

Art No. 02AZF300

Promo price: **72.00 €\***

Suggested retail price: ~~105.00 €\*~~



### Data Hold Unit

for Digital Caliper  
Art No. 959143  
Suggested retail price: 39.50 €\*  

---

### Extension Base, Depth Gauge

180mm width for up to 300mm Range  
Art No. 900370  
Suggested retail price: 69.00 €\*  

---



### Extension Base, Depth Gauge

260mm width for up to 300mm Range  
Art No. 900371  
Suggested retail price: 93.00 €\*  

---



### Extension Base, Depth Gauge

320mm width for up to 300mm Range  
Art No. 900372  
Suggested retail price: 107.00 €\*  

---



### Spare parts

Consumable spares:



## Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €\*  

---