

## Digital ABS Blade Caliper

Item number: 573-734-20

### Images



Dust- and  
Water-  
Protected

www.tuv.com  
ID 0000045042

# ABSOLUTE®

# IP67

### Description

A Mitutoyo waterproof digital caliper suitable for use in the presence of coolant or cutting oil. Equipped with special thin-ended jaws for outside measurement.


- The outside measuring faces are carbide.

### Features

<b>Digital/Analog:</b>	Digital
<b>Inch-Metric:</b>	Inch/Metric
<b>Range:</b>	0 - 6 "
<b>Graduation:</b>	0.0005"/0.01 mm
<b>Delivered:</b>	In a box with SR44 battery
<b>Thumb roller:</b>	Yes
<b>Max. Permissible Error E MPE:</b>	±0.001"/±0.02 mm
<b>Max. Permissible Error S MPE:</b>	±0.002"/±0.04 mm
<b>Max. response speed:</b>	Unlimited

<b>Display:</b>	LCD, character height 9 mm
<b>ORIGIN (ABS-Zero):</b>	Yes
<b>Auto Power OFF after 20 min. non use:</b>	Yes
<b>Low voltage alarm:</b>	Yes
<b>Data output:</b>	Yes
<b>Battery life:</b>	Approx. 5 years under normal use
<b>Mass:</b>	168 g

## Dimensions



## Accessories

### Optional accessories:

Promotion!

**Mitutoyo**

**MiCAT**  
the standard in world  
metrology software

**MeasurLink**

**USB-ITPAK**

**USB-ITPAK Vers. 3.0**

USB Dongle + Manual (Software available Online)

Art No. 06AGR543

**Promo price: 268.00 €\***

~~Suggested retail price: 340.00 €\*~~



### Digimatic Cable with Data Button IP Type

1 m, Caliper Type  
Art No. 05CZA624  
Suggested retail price: 100.00 €\*



### Digimatic Cable with Data Button IP Type

2 m, Caliper Type  
Art No. 05CZA625  
Suggested retail price: 107.00 €\*  
~~107.00 €\*  
107.00 €\*~~

Promotion!



### USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data Button IP Caliper Type  
Art No. 06AFM380A  
Promo price: **111.00 €\*  
Suggested retail price: 141.00 €\***

Promotion!



### U-WAVE fit, IP67 Type

Wireless Transmitter for Caliper  
Art No. 264-620  
Promo price: **129.00 €\*  
Suggested retail price: 185.00 €\***

Promotion!



### U-WAVE fit, Buzzer Type

Wireless Transmitter for Caliper  
Art No. 264-621  
Promo price: **129.00 €\*  
Suggested retail price: 185.00 €\***

Promotion!



### U-WAVE fit Bluetooth, IP67 Type

Wireless Transmitter for Caliper  
Art No. 264-624  
Promo price: **129.00 €\*  
Suggested retail price: 185.00 €\***

Promotion!



## U-WAVE fit Bluetooth, Buzzer Type

Wireless Transmitter for Caliper  
Art No. 264-625

Promo price: **129.00 €\***   
Suggested retail price: ~~185.00 €\*~~

Promotion!



## Connection Unit for IP Caliper, Micrometer

with Data Button for U-WAVE fit, U-WAVE fit Bluetooth

Art No. 02AZF310

Promo price: **76.00 €\***   
Suggested retail price: ~~110.00 €\*~~



## Depth Base Attachment for Caliper

75mm width for 100, 150, 200mm Range  
Art No. 050083-10

Suggested retail price: **60.00 €\***



## Depth Base Attachment for Caliper

100mm width for 100, 150, 200mm Range  
Art No. 050084-10

Suggested retail price: **67.00 €\***

### Spare parts

Consumable spares:



## Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €\*  

---