


# Anti Slip Mat Cushion-Dek™ 420

## Product Images





## Short Description

---

- Tough PVC compound molded with a raised pyramid design to enhance traction
- Made from 100% recycled PVC
- Drainage system for use in wet areas
- Slotted perforations (1/2" wide x 1-7/8" long) allow for moisture to escape worker platform
- Studded bottom surface raises mat and allows for channeling of moisture and continuous aeration

## Description

---

Cushion-Dek™ is made from a tough PVC compound molded with a raised pyramid design to enhance traction. Slotted perforations allow for moisture to drain from the worker platform in wet environments. A studded bottom surface raises the mat and allows for channeling of moisture.

## Specifications

---

Model No	420
Available Colors	Black
Overall Thickness	7/16
Roll Sizes	2'x 30'; 3'x 30'; 4'x 30'
Custom Lengths	2', 3' and 4' widths (up to 30' long)
Standard sizes	2'x 3'; 2'x 6'; 3'x 4'; 3'x 6'; 3'x 10'; 4'x 6'; 4'x 8'
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Wet/Dry and Oily Areas
Special Characteristics	Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals   Resistant to most chemicals
Recommended Use	For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations.
Special Remarks	Factory-assembled custom configurations available
Surface	Raised Pyramid Configuration
Edges	No borders
Usage Intensity	Heavy duty
Material Specifications	PVC (DOP free)
Process	Injection Molding
Weight Lbs/sqft	1.3
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Anti-Fatigue Rating	Better
Slip Resistance Rating	Better
Wear Resistance Rating	Better

# Prop 65

---

**⚠️WARNING:** This product can expose you to chemicals including di-2-ethylhexyl phthalate and/or diisononyl phthalate which is known to the State of California to cause cancer, birth defects or reproductive harm. For more information, visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

## Product Options

---

Dimensions:	2ft x 30ft
	2ft x 3ft
	2ft x 6ft
	2ft x Specify Length
	3ft x 10ft
	3ft x 30ft
	3ft x 4ft
	3ft x 6ft
	3ft x Specify Length
	4ft x 30ft
	4ft x 6ft
	4ft x 8ft
	4ft x Specify Length