



4' x 75', Blue, Marble Sof-Tyle[™] Anti Fatigue Mat, 470

Product Images





Short Description

- Heavy-duty vinyl marble-pattern top surface combined with a dense closed cell PVC foam base provides added cushioning comfort
- Smooth attractive surface easy to sweep clean
- UniFusion™ bond guaranteed for the life of the mat
- Redstop™ non-slip backing to reduce mat slippage
- Beveled edges on all 4 sides

Description

Marble Sof-Tyle™ is an anti-fatigue floor mat provides comfort and ergonomic support and complements any décor with a stylish smooth marble-pattern design. The durable vinyl top surface is easy to sweep clean or damp mop and is combined with a dense closed cell foam base utilizing NoTrax® exclusive UniFusion™ technology. This virtually eliminates the possibility of de-lamination. NoTrax® laminate floor mats that come with RedStop™, a uniquely engineered non-slip backing technology, eliminates the slipping and sliding of floor mats on smooth surface flooring such as tile, wood, marble, and treated concrete For dry applications such as lab testing area, check-out counters, order fulfillment lines and pharmacies. The sloped beveled edges reduce tripping hazards and allow easy access on and off the mat.

Specifications

Model No	470R0048BU
Color	Blue
Dimensions	4ft x 75ft
Thickness	1/2in
UPC	662641807037
Brand	NoTrax
Available Colors	Gray
Custom Lengths	2', 3' and 4' widths (up to 75' long)
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Dry Areas
Special Characteristics	Coefficient of friction NSF1 certified Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals
Recommended Use	For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations.
Special Remarks	Recommended where there is a minimal amount of debris in the environment and a concern for the mat to match a décor.
Edges	Beveled edges on all sides
Usage Intensity	Heavy duty
Material Specifications	PVC on microcellular vinyl base
Surface Detail	Marble Pattern
Backing	Closed Cell Polyvinylchloride with RedStop™ slip-resistant backing
Process	Lamination
Weight Lbs/sqft	1.2
Thickness Inch	1/2in
Fire Rating US	Pass

REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Anti-Fatigue Rating	Best
Slip Resistance Rating	Best
Wear Resistance Rating	Best

Prop 65

⚠️WARNING: This product can expose you to chemicals including di-2-ethylhexyl phthalate and/or diisononyl phthalate which is known to the State of California to cause cancer, birth defects or reproductive harm. For more information, visit www.P65Warnings.ca.gov.