



2" x 5', Female, Orange, M.D. Ramp System® for Cushion-Ease® Anti Fatigue Mat, 551

Product Images





Short Description

- Easy to snap together system for on-site custom work station platforms
- Nitrile provides highest level of resistance to chemicals, oils and greases
- Compatible with any Cushion-Ease® family mats
- Available as:
 - * 3 foot long Male/Female Ramps
 - * 5 foot long Male/Female Ramps

Description

The M.D. Ramp System® is designed for use with the Cushion-Ease® family of floor mats and provides a 2" beveled edge for easy access onto or off of the work platform. Made from a 100% nitrile base rubber compound M.D. Ramp Systems® provide the highest resistance to chemicals, cutting fluids, animal fats, oils and greases. All ramp lengths fit the male/female interlocking system on the mats and are beveled and molded with mitered corners and a protruding tab that locks together the two adjoining ramps for a secure, professional corner. Square edges can be achieved by trimming off the miter using the cut line on the bottom of the ramp.

Model No	551F0005OR
Color	Orange
Dimensions	2in x 60in
Thickness	3/4in
UPC	662641742253
Brand	NoTrax
Special Price Type	Sale
Available Colors	Black; Orange; Red; Yellow
Standard sizes	2"x3', 2"x5'
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Wet/Dry and Oily Areas
Special Characteristics	Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals Resistant to most industrial oils
Recommended Use	For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations.
Special Remarks	All ramp lengths are beveled and molded with mitered corners and a protruding tab. The tab locks together the two adjoining ramps for a secure, professional corner.
Edges	Attachable beveled edges are available
Usage Intensity	Heavy duty
Material Specifications	100% Nitrile rubber
Surface Detail	Ribbed
Process	Compression Molding
Weight Lbs/sqft	1.8
Thickness Inch	3/4in
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).

Specifications

Anti-Fatigue Rating	Best
Slip Resistance Rating	Best
Wear Resistance Rating	Best

Prop 65

⚠️WARNING: This product can expose you to chemicals including diisodecyl phthalate which is known to the State of California to cause birth defects or reproductive harm, and 2-mercaptobenzothiazole which is know to the State of California to cause cancer. For more information, visit www.P65Warnings.ca.gov.