


## 2' x Custom Length, Black-Yellow, Diamond Plate Runner<sup>™</sup> Anti-Slip Message Mats, 738

### Product Images





## Short Description

---

- Heavy-duty rubber diamond design improves traction and comfort
- Insulates floor and creates a silencing effect
- Oil, grease, and chemical resistant
- Provides barrier to cold floors and floor protection
- Low profile to eliminate trip hazards and allow for cart traffic

## Description

---

The high profile diamond-embossed top surface yields exceptional traction from any direction. Made of durable rubber, this runner is easy to sweep clean and has a low profile allowing for easy on/off cart traffic. Diamond Plate Runner™ is recommended for applications where safety and slip protection is needed with minimal anti-fatigue value such as aisles, warehouses, vending areas, and industrial passageways.

# Specifications

|                         |                                                                                                                             |
|-------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Model No                | 738C0024YB                                                                                                                  |
| Color                   | Black/Yellow                                                                                                                |
| Dimensions              | 2ft x Specify Length                                                                                                        |
| Thickness               | 5/32in                                                                                                                      |
| UPC                     | 662641827080                                                                                                                |
| Brand                   | NoTrax                                                                                                                      |
| Roll Sizes              | 2'x75', 3'x75', 4'x75'                                                                                                      |
| Custom Lengths          | 2', 3', 4' and 5' widths (up to 150' long)                                                                                  |
| Group                   | Ergonomic, Anti-fatigue & Safety Matting                                                                                    |
| Environment             | Dry Areas                                                                                                                   |
| Recommended Use         | For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations. |
| Special Remarks         | The diamond plate top surface provides additional traction                                                                  |
| Edges                   | No borders                                                                                                                  |
| Usage Intensity         | Light duty                                                                                                                  |
| Material Specifications | SBR Rubber                                                                                                                  |
| Surface Detail          | Industrial Diamond Plate                                                                                                    |
| Process                 | Calendering                                                                                                                 |
| Weight Lbs/sqft         | 0.8                                                                                                                         |
| Thickness Inch          | 5/32in                                                                                                                      |
| Anti-Fatigue Rating     | Good                                                                                                                        |
| Slip Resistance Rating  | Better                                                                                                                      |
| Wear Resistance Rating  | Better                                                                                                                      |

## Prop 65

---

 **WARNING:** This product can expose you to chemicals including di-2-ethylhexyl phthalate and/or diisononyl phthalate which is known to the State of California to cause cancer, birth defects or reproductive harm. For more information, visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).