
4' x 75', Black, Corrugated Switchboard Mat, 830

Product Images





Short Description

- Insulated matting engineered to protect workers from electric shock
- Electrically Insulative Type 2 PVC compound
- Corrugated top surface - Added traction and easy to sweep clean
- Class 2 Di-electric Strength: 30,000 volts
- Proof test of 20,000 volts

Description

Corrugated Switchboard Matting is a non-conductive floor matting made from a PVC compound, designed to provide insulation for the worker. The mat prevents the worker from being grounded, thereby eliminating the possibility of electrical shock. The corrugated saw-tooth top surface provides increased traction and is easy to sweep clean. Switchboard

matting is intended for use in dry environments in front of high voltage boxes, electrical fuse boxes, and transformers.

Specifications

| | |
|-------------------------|---|
| Model No | 830R0475BL |
| Color | Black |
| Dimensions | 4ft x 75ft |
| Thickness | 1/4in |
| UPC | 662641863392 |
| Available Colors | Black |
| Roll Sizes | 2'x75', 3'x75', 4'x75' |
| Custom Lengths | 2', 3' and 4' widths (up to 75' long) |
| Group | Ergonomic, Anti-fatigue & Safety Matting |
| Environment | Dry Areas |
| Special Characteristics | Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals Recommended maximum usage: 17.000 Volts |
| Recommended Use | Around electric sub-stations, transformers and switches, electrical panels, engine and generator rooms |
| Special Remarks | It is highly recommended that the mat be replaced every 12 months for optimum performance |
| Surface | Lengthwise Corrugated Rib Pattern |
| Edges | No borders |
| Usage Intensity | Heavy duty |
| Material Specifications | PVC (DOP free) |
| Process | Calendering |
| Weight Lbs/sqft | 1.7 |
| Thickness Inch | 1/4in |
| Voltage Class | 2 |
| Voltage Maximum | 20000 |
| Voltage Recommended | 17000 |

| | |
|------------------------|---|
| REACH Compliant | Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals). |
| Anti-Fatigue Rating | Good |
| Slip Resistance Rating | Best |
| Wear Resistance Rating | Best |

Prop 65

⚠️WARNING: This product can expose you to chemicals including di-2-ethylhexyl phthalate and/or diisononyl phthalate which is known to the State of California to cause cancer, birth defects or reproductive harm. For more information, visit www.P65Warnings.ca.gov.