



4' x Custom Length, Black, Marble Sof-Tyle[™] Grande[™] Anti Fatigue Mat, 970

Product Images





Short Description

- Heavy-duty vinyl marble-pattern top surface combined with a dense closed cell PVC foam base provides added cushioning comfort
- Smooth attractive surface easy to sweep clean
- UniFusion™ bond guaranteed for the life of the mat
- Redstop™ non-slip backing to reduce mat slippage
- Beveled edges on all 4 sides

Description

Marble Sof-Tyle™ Grande™ is an anti-fatigue floor mat provides the ultimate in comfort and ergonomic support at a full ONE-INCH thick. The stylish smooth marble-pattern design complements any décor and the durable vinyl top surface is easy to sweep clean or damp mop. The top surface is combined with a dense closed cell foam base utilizing NoTrax® exclusive UniFusion™ technology. This virtually eliminates the possibility of de-lamination. NoTrax® laminate floor mats that come with RedStop™, a uniquely engineered non-slip backing technology, eliminates the slipping and sliding of floor mats on smooth surface flooring such as tile, wood, marble, and treated concrete For dry applications such as lab testing area, check-out counters, order fulfillment lines and pharmacies. The sloped beveled edges reduce tripping hazards and allow easy access on and off the mat.

Model No	970C0048BL
Color	Black
Dimensions	4ft x Specify Length
Thickness	1in
UPC	662641750838
Brand	NoTrax
Custom Lengths	2', 3' and 4' widths (up to 75' long)
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Dry Areas
Special Characteristics	Coefficient of friction NSF1 certified Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals
Recommended Use	For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations.
Special Remarks	Recommended where there is a minimal amount of debris in the environment and a concern for the mat to match a décor. Full 1" thick version for applications that require additional comfort.
Edges	Beveled edges on all sides
Usage Intensity	Heavy duty
Material Specifications	PVC on microcellular vinyl base
Surface Detail	Marble Pattern
Backing	Closed Cell Polyvinylchloride with RedStop™ slip-resistant backing
Process	Lamination
Weight Lbs/sqft	1.5
Thickness Inch	1in
Fire Rating US	Pass
Specifications REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).

Anti-Fatigue Rating	Superior
Slip Resistance Rating	Superior
Wear Resistance Rating	Superior

Prop 65

⚠️WARNING: This product can expose you to chemicals including di-2-ethylhexyl phthalate and/or diisononyl phthalate which is known to the State of California to cause cancer, birth defects or reproductive harm. For more information, visit www.P65Warnings.ca.gov.