
2' x Custom Length, Black, ErgoMat™ Grande™ Anti Fatigue Mat, 974

Product Images



Short Description

- Heavy-duty corrugated ribbed top surface combined with a dense closed cell PVC foam base provides added cushioning comfort
- Corrugated ribbed texture provides traction and easy to sweep clean
- Ribbed texture runs the length of the mat
- UniFusion™ bond guaranteed for the life of the mat
- Redstop™ non-slip backing to reduce mat slippage

Description

Ergo Mat™ Grande™ is an anti-fatigue floor mat provides comfort and ergonomic support at a full ONE INCH thick. The durable vinyl corrugated ribbed top surface that provides directional traction to reduce slips and offers superior anti-fatigue support for applications where workers are required to stand for long periods of time such as packaging stations, shipping departments, welding areas, and assembly lines. The top surface is combined with a dense closed cell foam base utilizing NoTrax® exclusive UniFusion™ technology. This virtually eliminates the possibility of de-lamination. NoTrax® laminate floor mats that come with RedStop™, a uniquely engineered non-slip backing technology, eliminates the slipping and sliding of floor mats on smooth surface flooring such as tile, wood, marble, and treated concrete. The sloped beveled edges reduce tripping hazards and allow easy access on and off the mat.

Specifications

Model No	974C0024BL
Color	Black
Dimensions	2ft x Specify Length
Thickness	1in
UPC	662641750944
Brand	NoTrax
Roll Sizes	2'x75', 3'x75', 4'x75'
Custom Lengths	2', 3' and 4' widths (up to 75' long)
Standard sizes	2'x3', 3'x5', 3'x12'
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Dry Areas
Special Characteristics	Coefficient of friction NSF1 certified Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals
Recommended Use	In manufacturing plants, production lines, assembly lines, CNC machines, metal working, fabrication
Special Remarks	Ribs run the length of the mat providing directional traction to reduce slips. Full 1" thick version for applications that require additional comfort
Edges	Beveled edges on all sides
Usage Intensity	Heavy duty
Material Specifications	PVC on microcellular vinyl base
Surface Detail	Lengthwise Corrugated Rib Pattern
Backing	Closed Cell Polyvinylchloride with RedStop™ slip-resistant backing
Process	Lamination
Weight Lbs/sqft	1.5
Thickness Inch	1in
Fire Rating US	Pass

REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Anti-Fatigue Rating	Superior
Slip Resistance Rating	Superior
Wear Resistance Rating	Superior

Prop 65

⚠️WARNING: This product can expose you to chemicals including di-2-ethylhexyl phthalate and/or diisononyl phthalate which is known to the State of California to cause cancer, birth defects or reproductive harm. For more information, visit www.P65Warnings.ca.gov.