



# Drainage Anti-Fatigue Mat San-Eze® T12

## Product Images





## Short Description

---

- Raised edging around each hole creates a slip resistant surface
- Large drainage holes remove liquid and debris from platform
- Tested and certified by the National Sanitation Foundation (NSF) for grease and oil protection and durability (Brown only)
- 100% Nitrile Rubber compound for superior grease and oil resistance
- Free of DOP, DMF, ozone depleting substances, silicone and heavy metals
- Provides superior ergonomic comfort and traction in wet or greasy areas

## Description

---

One of the premier food service mats in the industry, San-EZE® is made from a 100% heavy-duty Nitrile rubber compound providing the ultimate in grease and oil resistance and is NSF tested and certified (brown only). San-EZE® is specially formulated to provide superior ergonomic comfort and traction in wet or greasy areas. A large hole drainage system facilitates the removal of liquids and debris from work areas further enhancing slip resistance.

## Specifications

---

|                          |   |
|--------------------------|---|
| Model No                 | T12   |
| Available Colors         | Black; Brown  |
| Overall Thickness        | 7/8   |
| Standard sizes           | 39"x 39"; 39"x 19.5"; 39"x 29.25"; 39"x 58.5"   |
| Group                    | Ergonomic, Anti-fatigue & Safety Matting  |
| Environment              | Wet/Dry and Greasy Areas  |
| Special Characteristics  | Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals |
| Recommended Use          | Restaurant kitchens, food prep, food processing environments  |
| Special Remarks          | Cleaning with detergent and power-washer is recommended for extended service life                       |
| Surface                  | Large Drainage Holes  |
| Edges                    | No borders  |
| Usage Intensity          | Heavy duty  |
| Material Specifications  | 100% Nitrile rubber   |
| Process                  | Compression Molding   |
| Weight Lbs/sqft          | 2.3   |
| Fire Rating US           | Pass  |
| Slip Resistance Rating   | Superior  |
| Comfort Rating           | Superior  |
| Grease Resistance Rating | Superior  |
| Wearability Rating       | Superior  |

## Prop 65

---

**⚠️WARNING:** This product can expose you to chemicals including diisodecyl phthalate which is known to the State of California to cause birth defects or reproductive harm. For more information, visit

## Product Options

---

|             |                 |
|-------------|-----------------|
| Color:      | Black           |
|             | Brown           |
| Dimensions: | 3.25ft x 3.25ft |
|             | 39in x 19in     |
|             | 39in x 29in     |
|             | 39in x 58in     |