


SPILL PALLETS

These secondary containment systems are engineered to meet the rigors of today's regulatory environment.

Raised edges on back and sides helps orient barrels on the pallet. Made from 100% polyethylene, these Spill Pallets provide excellent chemical resistance. All units are forkliftable and have removable grates for easy cleaning. Includes drain and plug.



IBC SPILL PALLET

Intermediate Bulk Containment made easy.

This IBC Spill Pallet gives intermediate bulk container users more versatile spill containment. It fits more than 99% of all IBC dispensing units and features a large sump capacity of 385 gallons, exceeding EPA regulations! This unit also has an integrated 5 gallon pail holder for quick and easy dispensing. Optional drain with plug available.

Typical installations for IBC tank.



- Forkliftable & Nestable for convenient shipment and storage
- 100% polyethylene construction will not rust or corrode or have adverse reactions with chemicals



SPILL PALLET	DIMENSIONS	WEIGHT	HANDLING CAPACITY	SUMP CAPACITY	REGULATIONS	PART #
2 Drum	53.5" l x 29" w x 17" h 135.89 cm x 73.66 cm x 43.18 cm	57 lbs. / 25.8 kg	2000 lbs. / 907 kg	58 gal. / 219.5 liters	EPA, 40 CRF 264.175, SPCC, UFC and NPDES	450612
4 Drum - In Line	98.25" l x 25.25" w x 11.5" h 249.56 cm x 64.135 cm x 29.21 cm	77 lbs. / 34.9 kg	3000 lbs. / 1360 kg	66 gal. / 249.8 liters	EPA, 40 CRF 264.175, SPCC, UFC and NPDES	450614-IL
4 Drum - Slim Line Low Profile - Square	51.5" l x 51.5" w x 8" h 130.81 cm x 130.81 cm x 20.32 cm	76 lbs. / 34.5 kg	8000 lbs. / 2722 kg	66 gal. / 249.8 liters	EPA, 40 CRF 264.175, SPCC, UFC and NPDES	450614-LP
IBC Spill Pallet	80" l x 73" w x 30" h 203.2 cm x 185.42 cm x 76 cm	293 lbs./ 132.9 kg	8000 lbs. / 2722 kg	385 gal. / 1457 liters	EPA, 40 CRF 264.175, SPCC, UFC and NPDES	450503

RAMP - 8"



PART # 450555

Designed for use with 450614-LP spill pallet.

- Ribbed, non-skid surface for safe walking
- 10° ramp slope
- 100% polyethylene construction
- **Dimensions:**
45.4" l x 32" w x 7.75" h
115 cm x 81 cm x 19.69 cm
- **Weight:**
65 lbs. / 29.5 kg
- **Handling Capacity:**
1000 lbs. / 453.6 kg

RAMP EXTENDER



PART # 450316

Designed for use with 450316 ramp and 450614-IL spill pallet.

- **Dimensions:**
29.5" l x 8.5" w x 5.5" h
74.93 cm x 21.59 cm x 13.97 cm
- **Weight:**
6 lbs. / 2.7 kg
- **Handling Capacity:**
1000 lbs. / 453.6 kg