



Drum Adapter Kit

Drum Adapter Kits allow breathers to be installed on any storage tank or drum; there's never been a cleaner, more effective way to store, filter and pump lubricants from a drum. Unique design ensures all fluid handling is managed through one adapter. Anodized aluminum adapters have colorized quick connects for pumping oil in and out of drum. Single-port access to the oil reduces contamination as drum remains closed. Off-line filtration units easily connect to adapter without ever disrupting the performance of the breather.

BODY HEIGHT	BODY DIAMETER	MOUNTING CONNECTION	SAMPLE PORT	GAUGE PORT	PIPE DIAMETER AND LENGTH
4.75	2.5	2" MNPT	Yes Model A-650	Yes Model A-655	0.5" D x 12" L (oil in) and 0.75" D x 32" L (oil out)
CONNECTOR	ADAPTER	PART NUMBER		ADAPTER	PART NUMBER
None	No Quick Disconnects	960NQ			
Male disconnects only	ISO B connects	960ISOM		Mid Green	960MGM
	Beige	960BGM		Orange	960ORM
	Black	960BKM		Purple	960PLM
	Blue	960BLM		Red	960RDM
	Dark Green	960DGM		Silver	960SLM
	Dark Grey	960GYM		Yellow	960YLM
Male and Female disconnects	ISO B connects	960ISOMF		Mid Green	960MGMF
	Beige	960BGMF		Orange	960ORMF
	Black	960BKMF		Purple	960PLMF
	Blue	960BLMF		Red	960RDMF
	Dark Green	960DGMF		Silver	960SLMF
	Dark Grey	960GYMF		Yellow	960YLMF



Hydraulic Reservoir Adapter Kit

Hydraulic Reservoir Adapter Kits allow breathers to be installed on any hydraulic fluid tank or reservoir. The patent-pending aluminum adapters have colorized quick connects in two sizes for pumping oil in and out, allowing the system to remain closed at all times, dramatically reducing contamination while improving oil-handling safety. Off-line filtration can also be connected through the adapter without ever disrupting the breather or opening the tank.

BODY HEIGHT	BODY DIAMETER	MOUNTING CONNECTION	SAMPLE PORT	GAUGE PORT	PIPE DIAMETER AND LENGTH
1.875	3.5	ANSI 6 hole pattern flange	Yes Model A-650	Yes Model A-655	0.5" D x 12" L
CONNECTOR	ADAPTER	PART NUMBER		ADAPTER	PART NUMBER
None	No Quick Disconnects	961NQ			
Male disconnects only	ISO B connects	961ISOM		Mid Green	961MGM
	Beige	961BGM		Orange	961ORM
	Black	961BKM		Purple	961PLM
	Blue	961BLM		Red	961RDM
	Dark Green	961DGM		Silver	961SLM
	Dark Grey	961GYM		Yellow	961YLM
Male and Female disconnects	ISO B connects	961ISOMF		Mid Green	961MGMF
	Beige	961BGMF		Orange	961ORMF
	Black	961BKMF		Purple	961PLMF
	Blue	961BLMF		Red	961RDMF
	Dark Green	961DGMF		Silver	961SLMF
	Dark Grey	961GYMF		Yellow	961YLMF