


Tube to Tube Unions

Drop Size Tees

for Fractional Tube

Eliminates the extra connection when adapting with a tube stub reducer



CPI™ Part No.	A-LOK® Part No.	Interchanges With	T1 Tube O.D.	T2 Tube O.D.	T3 Tube O.D.
4-4-2 JBZ	4-4-2 JLZ	400-3-4-2	1/4	1/4	1/8
6-6-4 JBZ	6-6-4 JLZ	600-3-6-4	3/8	3/8	1/4
6-4-6 JBZ	6-4-6 JLZ	600-3-4-6	3/8	1/4	3/8
6-4-4 JBZ	6-4-4 JLZ	600-3-4-4	3/8	1/4	1/4
8-8-6 JBZ	8-8-6 JLZ	810-3-8-6	1/2	1/2	3/8
8-8-4 JBZ	8-8-4 JLZ	810-3-8-4	1/2	1/2	1/4
8-6-8 JBZ	8-6-8 JLZ	810-3-6-8	1/2	3/8	1/2
8-4-8 JBZ	8-4-8 JLZ	810-3-4-8	1/2	1/4	1/2
8-6-6 JBZ	8-6-6 JLZ	810-3-6-6	1/2	3/8	3/8
8-4-4 JBZ	8-4-4 JLZ	810-3-4-4	1/2	1/4	1/4
10-10-8 JBZ	10-10-8 JLZ	1010-3-10-8	5/8	5/8	1/2
10-10-6 JBZ	10-10-6 JLZ	1010-3-10-6	5/8	5/8	3/8
10-8-8 JBZ	10-8-8 JLZ	1010-3-8-8	5/8	1/2	1/2
10-8-6 JBZ	10-8-6 JLZ	1010-3-8-6	5/8	1/2	3/8
10-6-6 JBZ	10-6-6 JLZ	1010-3-6-6	5/8	3/8	3/8
10-6-8 JBZ	10-6-8 JLZ	1010-3-6-8	5/8	3/8	1/2
12-12-10 JBZ	12-12-10 JLZ	1210-3-12-10	3/4	3/4	5/8
12-12-8 JBZ	12-12-8 JLZ	1210-3-12-8	3/4	3/4	1/2
12-12-6 JBZ	12-12-6 JLZ	1210-3-12-6	3/4	3/4	3/8
12-12-4 JBZ	12-12-4 JLZ	1210-3-12-4	3/4	3/4	1/4
12-10-10 JBZ	12-10-10 JLZ	1210-3-10-10	3/4	5/8	5/8
12-8-8 JBZ	12-8-8 JLZ	1210-3-8-8	3/4	1/2	1/2
12-6-6 JBZ	12-6-6 JLZ	1210-3-6-6	3/4	3/8	3/8
12-10-8 JBZ	12-10-8 JLZ	1210-3-10-8	3/4	5/8	1/2
12-10-6 JBZ	12-10-6 JLZ	1210-3-10-6	3/4	5/8	3/8
12-8-6 JBZ	12-8-6 JLZ	1210-3-8-6	3/4	1/2	3/8
14-14-6 JBZ	14-14-6 JLZ	1410-3-14-6	7/8	7/8	3/8
14-14-4 JBZ	14-14-4 JLZ	1410-3-14-4	7/8	7/8	1/4
14-12-12 JBZ	14-12-12 JLZ	1410-3-12-12	7/8	3/4	3/4
14-12-8 JBZ	14-12-8 JLZ	1410-3-12-8	7/8	3/4	1/2
14-12-6 JBZ	14-12-6 JLZ	1410-3-12-6	7/8	3/4	3/8
14-10-6 JBZ	14-10-6 JLZ	1410-3-10-6	7/8	5/8	3/8

For metric fittings and additional thread types, please see Catalog 4230/4233.

CPI™/A-LOK® Tube Fittings and Instrumentation Valves

CAT4200-PC | Aug 2023 | www.Parker.com/ipd

