



## Add-On Kits

Additional Add-On kits allow you to expand your Starter kit by sharing a set of posts. Configuration options include side to side, back to back and right angles (L-Shape). Add-On kits come complete with 2 posts, 4 or 5 shelves and 8 or 10 S-Hooks. Additional shelves and posts may be purchased separately. See chart on pg. 98. Units with Add-On kit cannot be made mobile. **Finishes:** Chrome, Stainless Steel, Proform Green, Gray and Black Epoxy

**600-800 lb.**  
**LOAD CAPACITY**  
**PER SHELF**

## TO CHOOSE FINISH ADD FINISH SUFFIX TO MODEL NO.

Ex: **Chrome**  
**Stainless**  
**Proform Green**  
**Gray**  
**Black**

WR86-1236**C**  
WR86-1236**S**  
WR86-1236**P**  
WR86-1236**GY**  
WR86-1236**BK**

Ex: **Chrome**  
**Stainless**  
**Proform Green**  
**Gray**  
**Black**


WR86-1236**C**-5  
WR86-1236**S**-5  
WR86-1236**P**-5  
WR86-1236**GY**-5  
WR86-1236**BK**-5

**Chrome**  
**Stainless**  
**Proform Green**  
**GY** Gray  
**BK** Black

|                  | 86"H - WIRE SHELVING 4 SHELVES |             |              |             | 86"H - WIRE SHELVING 5 SHELVES |             |              |             | AVAILABLE |   |   |    |    |  |
|------------------|--------------------------------|-------------|--------------|-------------|--------------------------------|-------------|--------------|-------------|-----------|---|---|----|----|--|
|                  | STARTER KIT                    |             | ADD-ON KIT   |             | STARTER KIT                    |             | ADD-ON KIT   |             | FINISHES  |   |   |    |    |  |
| SHELF<br>W" x L" | MODEL<br>NO.                   | SHIP<br>WGT | MODEL<br>NO. | SHIP<br>WGT | MODEL<br>NO.                   | SHIP<br>WGT | MODEL<br>NO. | SHIP<br>WGT | C         | S | P | GY | BK |  |
| 12" x 36"        | WR86-1236                      | 48 lbs      | AD86-1236    | 40 lbs      | WR86-1236-5                    | 55 lbs      | AD86-1236-5  | 49 lbs      | Y         | Y | Y | Y  | Y  |  |
| 12" x 42"        | WR86-1242                      | 52 lbs      | AD86-1242    | 44 lbs      | WR86-1242-5                    | 60 lbs      | AD86-1242-5  | 54 lbs      | Y         | N | Y | Y  | Y  |  |
| 12" x 48"        | WR86-1248                      | 56 lbs      | AD86-1248    | 48 lbs      | WR86-1248-5                    | 65 lbs      | AD86-1248-5  | 59 lbs      | Y         | Y | Y | Y  | Y  |  |
| 12" x 60"        | WR86-1260                      | 64 lbs      | AD86-1260    | 56 lbs      | WR86-1260-5                    | 78 lbs      | AD86-1260-5  | 72 lbs      | Y         | Y | Y | Y  | Y  |  |
| 12" x 72"        | WR86-1272                      | 72 lbs      | AD86-1272    | 64 lbs      | WR86-1272-5                    | 89 lbs      | AD86-1272-5  | 83 lbs      | Y         | Y | Y | Y  | Y  |  |
| 14" x 24"        | WR86-1424                      | 44 lbs      | AD86-1424    | 36 lbs      | WR86-1424-5                    | 50 lbs      | AD86-1424-5  | 44 lbs      | Y         | N | Y | Y  | Y  |  |
| 14" x 30"        | WR86-1430                      | 48 lbs      | AD86-1430    | 40 lbs      | WR86-1430-5                    | 55 lbs      | AD86-1430-5  | 49 lbs      | Y         | Y | Y | Y  | Y  |  |
| 14" x 36"        | WR86-1436                      | 52 lbs      | AD86-1436    | 44 lbs      | WR86-1436-5                    | 60 lbs      | AD86-1436-5  | 54 lbs      | Y         | Y | Y | Y  | Y  |  |
| 14" x 42"        | WR86-1442                      | 60 lbs      | AD86-1442    | 52 lbs      | WR86-1442-5                    | 70 lbs      | AD86-1442-5  | 64 lbs      | Y         | Y | Y | Y  | Y  |  |
| 14" x 48"        | WR86-1448                      | 64 lbs      | AD86-1448    | 56 lbs      | WR86-1448-5                    | 75 lbs      | AD86-1448-5  | 69 lbs      | Y         | Y | Y | Y  | Y  |  |
| 14" x 54"        | WR86-1454                      | 68 lbs      | AD86-1454    | 60 lbs      | WR86-1454-5                    | 80 lbs      | AD86-1454-5  | 74 lbs      | Y         | Y | Y | Y  | Y  |  |
| 14" x 60"        | WR86-1460                      | 76 lbs      | AD86-1460    | 68 lbs      | WR86-1460-5                    | 90 lbs      | AD86-1460-5  | 84 lbs      | Y         | Y | Y | Y  | Y  |  |
| 14" x 72"        | WR86-1472                      | 88 lbs      | AD86-1472    | 80 lbs      | WR86-1472-5                    | 105 lbs     | AD86-1472-5  | 99 lbs      | Y         | Y | Y | Y  | Y  |  |
| 18" x 24"        | WR86-1824                      | 48 lbs      | AD86-1824    | 40 lbs      | WR86-1824-5                    | 55 lbs      | AD86-1824-5  | 49 lbs      | Y         | Y | Y | Y  | Y  |  |
| 18" x 30"        | WR86-1830                      | 52 lbs      | AD86-1830    | 44 lbs      | WR86-1830-5                    | 60 lbs      | AD86-1830-5  | 54 lbs      | Y         | Y | Y | Y  | Y  |  |
| 18" x 36"        | WR86-1836                      | 60 lbs      | AD86-1836    | 52 lbs      | WR86-1836-5                    | 60 lbs      | AD86-1836-5  | 64 lbs      | Y         | Y | Y | Y  | Y  |  |
| 18" x 42"        | WR86-1842                      | 64 lbs      | AD86-1842    | 56 lbs      | WR86-1842-5                    | 75 lbs      | AD86-1842-5  | 69 lbs      | Y         | Y | Y | Y  | Y  |  |
| 18" x 48"        | WR86-1848                      | 68 lbs      | AD86-1848    | 60 lbs      | WR86-1848-5                    | 82 lbs      | AD86-1848-5  | 76 lbs      | Y         | Y | Y | Y  | Y  |  |
| 18" x 54"        | WR86-1854                      | 80 lbs      | AD86-1854    | 72 lbs      | WR86-1854-5                    | 95 lbs      | AD86-1854-5  | 89 lbs      | Y         | Y | Y | Y  | Y  |  |
| 18" x 60"        | WR86-1860                      | 88 lbs      | AD86-1860    | 80 lbs      | WR86-1860-5                    | 105 lbs     | AD86-1860-5  | 99 lbs      | Y         | Y | Y | Y  | Y  |  |
| 18" x 72"        | WR86-1872                      | 100 lbs     | AD86-1872    | 92 lbs      | WR86-1872-5                    | 120 lbs     | AD86-1872-5  | 114 lbs     | Y         | Y | Y | Y  | Y  |  |
| 21" x 24"        | WR86-2124                      | 52 lbs      | AD86-2124    | 44 lbs      | WR86-2124-5                    | 60 lbs      | AD86-2124-5  | 54 lbs      | Y         | Y | Y | Y  | Y  |  |
| 21" x 30"        | WR86-2130                      | 56 lbs      | AD86-2130    | 48 lbs      | WR86-2130-5                    | 65 lbs      | AD86-2130-5  | 59 lbs      | Y         | Y | Y | Y  | Y  |  |
| 21" x 36"        | WR86-2136                      | 64 lbs      | AD86-2136    | 56 lbs      | WR86-2136-5                    | 75 lbs      | AD86-2136-5  | 69 lbs      | Y         | Y | Y | Y  | Y  |  |
| 21" x 42"        | WR86-2142                      | 68 lbs      | AD86-2142    | 60 lbs      | WR86-2142-5                    | 80 lbs      | AD86-2142-5  | 74 lbs      | Y         | Y | Y | Y  | Y  |  |
| 21" x 48"        | WR86-2148                      | 76 lbs      | AD86-2148    | 68 lbs      | WR86-2148-5                    | 90 lbs      | AD86-2148-5  | 84 lbs      | Y         | Y | Y | Y  | Y  |  |
| 21" x 54"        | WR86-2154                      | 84 lbs      | AD86-2154    | 76 lbs      | WR86-2154-5                    | 100 lbs     | AD86-2154-5  | 94 lbs      | Y         | Y | Y | Y  | Y  |  |
| 21" x 60"        | WR86-2160                      | 92 lbs      | AD86-2160    | 84 lbs      | WR86-2160-5                    | 110 lbs     | AD86-2160-5  | 104 lbs     | Y         | Y | Y | Y  | Y  |  |
| 21" x 72"        | WR86-2172                      | 116 lbs     | AD86-2172    | 108 lbs     | WR86-2172-5                    | 140 lbs     | AD86-2172-5  | 134 lbs     | Y         | Y | Y | Y  | Y  |  |
| 24" x 24"        | WR86-2424                      | 56 lbs      | AD86-2424    | 48 lbs      | WR86-2424-5                    | 65 lbs      | AD86-2424-5  | 59 lbs      | Y         | Y | Y | Y  | Y  |  |
| 24" x 30"        | WR86-2430                      | 64 lbs      | AD86-2430    | 56 lbs      | WR86-2430-5                    | 75 lbs      | AD86-2430-5  | 69 lbs      | Y         | Y | Y | Y  | Y  |  |
| 24" x 36"        | WR86-2436                      | 72 lbs      | AD86-2436    | 64 lbs      | WR86-2436-5                    | 85 lbs      | AD86-2436-5  | 79 lbs      | Y         | Y | Y | Y  | Y  |  |
| 24" x 42"        | WR86-2442                      | 80 lbs      | AD86-2442    | 72 lbs      | WR86-2442-5                    | 95 lbs      | AD86-2442-5  | 89 lbs      | Y         | Y | Y | Y  | Y  |  |
| 24" x 48"        | WR86-2448                      | 84 lbs      | AD86-2448    | 76 lbs      | WR86-2448-5                    | 100 lbs     | AD86-2448-5  | 94 lbs      | Y         | Y | Y | Y  | Y  |  |
| 24" x 54"        | WR86-2454                      | 92 lbs      | AD86-2454    | 84 lbs      | WR86-2454-5                    | 110 lbs     | AD86-2454-5  | 104 lbs     | Y         | Y | Y | Y  | Y  |  |
| 24" x 60"        | WR86-2460                      | 104 lbs     | AD86-2460    | 96 lbs      | WR86-2460-5                    | 125 lbs     | AD86-2460-5  | 119 lbs     | Y         | Y | Y | Y  | Y  |  |
| 24" x 72"        | WR86-2472                      | 124 lbs     | AD86-2472    | 116 lbs     | WR86-2472-5                    | 150 lbs     | AD86-2472-5  | 144 lbs     | Y         | Y | Y | Y  | Y  |  |
| 30" x 36"        | WR86-3036                      | 80 lbs      | AD86-3036    | 72 lbs      | WR86-3036-5                    | 95 lbs      | AD86-3036-5  | 89 lbs      | Y         | Y | Y | Y  | Y  |  |
| 30" x 42"        | WR86-3042                      | 92 lbs      | AD86-3042    | 84 lbs      | WR86-3042-5                    | 110 lbs     | AD86-3042-5  | 104 lbs     | Y         | Y | Y | Y  | Y  |  |
| 30" x 48"        | WR86-3048                      | 104 lbs     | AD86-3048    | 96 lbs      | WR86-3048-5                    | 125 lbs     | AD86-3048-5  | 119 lbs     | Y         | Y | Y | Y  | Y  |  |
| 30" x 60"        | WR86-3060                      | 128 lbs     | AD86-3060    | 120 lbs     | WR86-3060-5                    | 155 lbs     | AD86-3060-5  | 149 lbs     | Y         | Y | Y | Y  | Y  |  |
| 30" x 72"        | WR86-3072                      | 144 lbs     | AD86-3072    | 136 lbs     | WR86-3072-5                    | 175 lbs     | AD86-3072-5  | 169 lbs     | Y         | Y | Y | Y  | Y  |  |
| 36" x 36"        | WR86-3636                      | 92 lbs      | AD86-3636    | 84 lbs      | WR86-3636-5                    | 110 lbs     | AD86-3636-5  | 104 lbs     | Y         | Y | Y | Y  | Y  |  |
| 36" x 48"        | WR86-3648                      | 112 lbs     | AD86-3648    | 104 lbs     | WR86-3648-5                    | 135 lbs     | AD86-3648-5  | 129 lbs     | Y         | Y | Y | Y  | Y  |  |
| 36" x 60"        | WR86-3660                      | 136 lbs     | AD86-3660    | 128 lbs     | WR86-3660-5                    | 165 lbs     | AD86-3660-5  | 159 lbs     | Y         | Y | Y | Y  | Y  |  |
| 36" x 72"        | WR86-3672                      | 144 lbs     | AD86-3672    | 136 lbs     | WR86-3672-5                    | 179 lbs     | AD86-3672-5  | 173 lbs     | Y         | Y | Y | Y  | Y  |  |

Shelving units include 4 posts and 4 or 5 shelves. Add-On units include 2 posts, 4 or 5 shelves and 8 or 10 S-Hooks.

Y (Yes) N (No)



## S-HOOKS

For continuous runs of shelving. Two hooks should be placed per shelf where two posts are not utilized.

