

Beveled Edge Anti-Fatigue Mat Diamond-Tuff™ Max 510

Product Images





Short Description

- Durable diamond pattern vinyl laminate top surface for added traction
- Dense closed cell PVC foam base provides added cushioning comfort
- Beveled edges on all 4 sides

Description

Diamond-Tuff™ Max is a durable anti-fatigue/anti-slip mat with a vinyl diamond plate top surface that provides sure footing and a full 1" thick foam base to provide the ultimate relief for leg and back discomfort in work applications where standing occurs for long periods of time. Diamond-Tuff™ Max is available in both workstation sizes and full rolls for applications that require a longer mat such as assembly lines. The non-directional diamond plate top surface is easy to sweep or damp mop clean. The sloped beveled edges reduce tripping hazards and allow easy access on and off the mat.

Specifications

Model No	510
Available Colors	Black; Black/Yellow
Overall Thickness	1
Roll Sizes	2'x 75'; 3'x 75'; 4'x 75'; 5'x 75'
Standard sizes	2'x 3'; 3'x 5'; 3'x 12'
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Dry Areas
Special Characteristics	Free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals
Recommended Use	For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations.
Special Remarks	The Diamond-Tuff™ series comes in 9/16" and a full 1" versions and allow you to select your level of comfort.
Surface	Industrial Diamond Plate
Edges	Beveled edges on all sides
Usage Intensity	Medium duty
Installation	No installation required
Material Specifications	PVC
Backing	Closed Cell Polyvinylchloride
Process	Lamination
Weight Lbs/sqft	1.5
Fire Rating US	Pass
Anti-Fatigue Rating	Better
Slip Resistance Rating	Best
Wear Resistance Rating	Better

Prop 65

⚠️WARNING: This product can expose you to chemicals including di-2-ethylhexyl phthalate and/or diisononyl phthalate which is known to the State of California to cause cancer, birth defects or reproductive harm. For more information, visit www.P65Warnings.ca.gov.

Product Options

Color:	Black
	Black/Yellow
Dimensions:	2ft x 3ft
	2ft x 75ft
	2ft x Specify Length
	3ft x 12ft
	3ft x 5ft
	3ft x 75ft
	3ft x Specify Length
	4ft x 75ft
	4ft x Specify Length
	5ft x 75ft
	5ft x Specify Length