


NPT Female Connector For fractional tube



CPI™ Part No.	A-LOK® Part No.	Inter- changes With	Tube O.D.	NPT Thread Size
1-1 GBZ	1FSC1N	100-7-1	1/16	1/16
1-2 GBZ	1FSC2N	100-7-2	1/16	1/8
2-2 GBZ	2FSC2N	200-7-2	1/8	1/8
2-4 GBZ	2FSC4N	200-7-4	1/8	1/4
3-2 GBZ	3FSC2N	300-7-2	3/16	1/8
3-4 GBZ	3FSC4N	300-7-4	3/16	1/4
4-2 GBZ	4FSC2N	400-7-2	1/4	1/8
4-4 GBZ	4FSC4N	400-7-4	1/4	1/4
4-6 GBZ	4FSC6N	400-7-6	1/4	3/8
4-8 GBZ	4FSC8N	400-7-8	1/4	1/2
5-2 GBZ	5FSC2N	500-7-2	5/16	1/8
5-4 GBZ	5FSC4N	500-7-4	5/16	1/4
5-6 GBZ	5FSC6N	500-7-6	5/16	3/8
6-2 GBZ	6FSC2N	600-7-2	3/8	1/8
6-4 GBZ	6FSC4N	600-7-4	3/8	1/4
6-6 GBZ	6FSC6N	600-7-6	3/8	3/8
6-8 GBZ	6FSC8N	600-7-8	3/8	1/2
6-12 GBZ	6FSC12N	600-7-12	3/8	3/4
8-4 GBZ	8FSC4N	810-7-4	1/2	1/4
8-6 GBZ	8FSC6N	810-7-6	1/2	3/8
8-8 GBZ	8FSC8N	810-7-8	1/2	1/2
8-12 GBZ	8FSC12N	810-7-12	1/2	3/4
10-6 GBZ	10FSC6N	1010-7-6	5/8	3/8
10-8 GBZ	10FSC8N	1010-7-8	5/8	1/2
10-12 GBZ	10FSC12N	1010-7-12	5/8	3/4
12-8 GBZ	12FSC8N	1210-7-8	3/4	1/2
12-12 GBZ	12FSC12N	1210-7-12	3/4	3/4
14-12 GBZ	14FSC12N	1410-7-12	7/8	3/4
16-12 GBZ	16FSC12N	1610-7-12	1	3/4
16-16 GBZ	16FSC16N	1610-7-16	1	1
20-20 GBZ	20FSC20N	2010-7-20	1-1/4	1-1/4
24-24 GBZ	24FSC24N	2410-7-24	1-1/2	1-1/2
32-32 GBZ	32FSC32N	3210-7-32	2	2

NOTE: Sizes 20, 24, 32 require additional lubrication prior to assembly.

For metric fittings and additional thread types, please see Catalog 4230/4233.