

DL1BDB3

LED bulb, Harmony XVB, BA 15d, green, steady light, 24V AC/DC



Main

| | |
|---------------------------------------|---|
| Range Compatibility | Harmony XVB Harmony XVD Harmony XVP |
| Accessory / separate part designation | Protected LED bulb |
| Accessory / Separate Part Type | LED bulb |
| Accessory / separate part category | Lighting accessories |
| Accessory / separate part destination | Beacon and indicator bank |
| [Us] rated supply voltage | 24 V AC/DC |
| Signalling type | Steady |
| Signalling colour | Green |
| Sale per indivisible quantity | 1 |

Complementary

| | |
|---------------------|------------------------|
| Current Consumption | 47 mA |
| Bulb base | BA 15d |
| Net Weight | 0.03 lb(US) (0.015 kg) |

Ordering and shipping details

| | |
|-------------------|-----------------------|
| Category | 22611-XVB-STACKLIGHTS |
| Discount Schedule | XV |
| GTIN | 3389110117905 |
| Returnability | Yes |
| Country of origin | ID |

Packing Units

| | |
|------------------------------|--------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1.38 in (3.5 cm) |
| Package 1 Width | 1.77 in (4.5 cm) |
| Package 1 Length | 2.36 in (6.0 cm) |
| Package 1 Weight | 0.39 oz (11.0 g) |
| Unit Type of Package 2 | S01 |
| Number of Units in Package 2 | 60 |
| Package 2 Height | 5.91 in (15.0 cm) |
| Package 2 Width | 5.91 in (15.0 cm) |
| Package 2 Length | 15.75 in (40.0 cm) |
| Package 2 Weight | 34.81 oz (987.0 g) |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|