

Product availability: Stock - Normally stocked in distribution facility



Main

| | |
|---------------------------|----------------------|
| Range | TeSys |
| Device short name | LUA |
| Product or component type | Limiter disconnecter |

Complementary

| | |
|--|--|
| Product compatibility | LUB LU2B |
| [I _{th}] conventional free air thermal current | 32 A |
| Breaking capacity | 70 KA 690 V 130 kA |
| Mounting mode | Direct |
| [U _i] rated insulation voltage | 690 V EN 60947-1 690 V IEC 60947-1 |
| I _{rms} rated making capacity | 50 kA |
| Connections - terminals | Connector 1 x 0.00...0.02 in ² (1...10 mm ²) flexible without cable end Connector 1 x 0.00...0.01 in ² (1...6 mm ²) flexible with cable end Connector 2 x 0.00...0.01 in ² (1...6 mm ²) flexible with cable end Connector 2 x 0.00...0.01 in ² (1...6 mm ²) flexible without cable end Connector 1 x 0.00...0.02 in ² (1.5...10 mm ²) solid Connector 2 x 0.00...0.01 in ² (1.5...6 mm ²) solid |
| Tightening torque | 16.82...22.13 Lbf.in (1.9...2.5 N.m) flat Ø 6 mm 16.82...22.13 lbf.in (1.9...2.5 N.m) Philips No 2 |
| Product weight | 0.68 lb(US) (0.31 kg) |

Ordering and shipping details

| | |
|---------------------|------------------------------|
| Category | 22399 - TESYS U, ACCESSORIES |
| Discount Schedule | I11 |
| GTIN | 00785901291817 |
| Package weight(Lbs) | 0.34 kg (0.75 lb(US)) |
| Returnability | Yes |
| Country of origin | MX |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| RECh Regulation | RECh Declaration |
| RECh free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |

| | |
|--------------------------|--|
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|