

**CODE NUMBER**

3400337

**DESCRIPTION**

1.28 gpf, Brushed Stainless Finish, Fixture Connection Rear Spud, Single Flush, Sensor-Operated, Short V500A & Adjustable Flush Connection Vacuum Breaker, Front Accessible Wall Box, Floor-mounted, CX Concealed Sensor Floor-mounted Water Closet Flushometer.

**DETAILS**

- Flush Volume: 1.28 gpf (4.8 Lpf)
- Finish: Brushed Stainless (SF)
- Valve: Piston
- Valve Body Material: Semi-red Brass
- Fixture Type: Water Closet
- Closet Mounting: Floor-mounted
- Fixture Connection: Rear Spud
- Wall Box: Front Accessible
- Vacuum Breaker: Short V500A & Adjustable Flush Connection

**FEATURES**


- Fixed volume piston with filtered O-ring bypass
- Front access wall plate requires no rear access plumbing chase
- Sensor activated, hands-free operation
- Battery operated with hardwired option
- Electronic override button
- Low battery indicator light
- Vandal resistant wall plate
- Adjustable flush connection

**VIDEOS**

- CX Flushometer Product Video
- CX Flushometer - Sensor Installation
- CX Flushometer - Sensor Vacuum Service
- CX Flushometer - Sensor Piston Service
- CX Flushometer Product Video (Spanish)
- PVD Special Finishes



**COMPLIANCES & CERTIFICATIONS**



(ADA Compliant, BAA Compliant, BABAA Compliant, cUPC Certified, EPD, HPD, LEED Materials & Resources EPD Credit, LEED Materials & Resources HPD Credit, WaterSense Listed)

**ELECTRICAL SPECIFICATIONS**

- Self-Adaptive Window: ±12
- Sensor Range: 22" - 46" (559 - 1,168mm)
- Solenoid Operator: 6 VAC
- Transformers (specify separately):
  - EL-386 (Up to 1 flushometer)
  - EL-451 (up to 6 flushometers)

**DOWNLOADS**

- [CX 8158/8198 Installation Instructions](#)
- [CX 8158/8198 Repair and Maintenance Guide](#)
- [Additional Downloads](#)

**NOTES**

All information contained within this document subject to change without notice.

Looking for other variations of the CX 8154 product? [View the general spec sheet with all options.](#)

WaterSense compliant when used with a WaterSense compliant fixture

**WARRANTY**

[View Warranty Information](#)

**Sloan 10500 Seymour Ave, Franklin Park, IL 60131**

Phone: 800.982.5839 • Fax: 800.447.8329 • [sloan.com](http://sloan.com)


**ROUGH-IN**

**MODEL 8154  
CLOSET  
FLOOR MOUNT  
REAR INLET**

**SIDE VIEW**

**FRONT VIEW**

**!!! IMPORTANT !!!**  
**ACCURACY IS IMPORTANT FOR  
 WALL OPENING DIMENSIONS.  
 VALVE MUST BE CENTERED  
 HORIZONTALLY IN OPENING  
 WITHIN 1/8". FOR ASSITANCE,  
 PLEASE CONSULT ROUGH-IN  
 TEMPLATE.**



Sloan 10500 Seymour Ave, Franklin Park, IL 60131  
 Phone: 800.982.5839 • Fax: 800.447.8329 • [sloan.com](http://sloan.com)