

Discharge Silencer Frames for PD Blowers

BBF Series 2" - 6"

Blower Market Solutions

Maximize Productivity - From junior to experienced technicians, assemble & ship blower packages faster with fewer resources.

Significant Costs Savings - Only one vendor needed to help you improve margins through lower labour and material handling costs.

Engineering Support - Design specifications and drawings are available to help you configure and present your package to your customers.

Ultra Compact Design - Integrated Discharge Silencer offers a low profile and small footprint.

Build Your Sound Enclosure Competitively - The compact design allows you to build significantly smaller and less costly enclosures to meet more stringent noise level requirements.

Benefits

- Low profile allows for easier maintenance inspections
- Quick installation time
- Cost savings (minimal packaging, freight & storage)
- Sound enclosures are more economical due to compact frame footprint
- Engineering support provided by Solberg for sizing specifications and specific requirements

Features

- Reactive style silencing design
- Integrated discharge silencer
- Adjustable motor supports for belt tensioning
- Pre-assembled rails to frame
- Corrosive resistant black powder coat carbon steel
- Assembly hardware included




Technical Specifications

- Pressure rating: 14.7 PSIG
- Hardware kit included (USA std. nuts, bolts, washers)
- Ports for relief valve, pressure & temperature gauges

Options

- Purpose built belt guard
- Flexible boot kit (clamp, flex adapter)
- Flange adapters
- Snubber discharge silencer for vacuum applications
- Contact factory for best Solberg filter for your package



Pipe Stub Inlet	MPT Outlet	Assembly SCFM Rating	Part Number	Dimensions (inches)			Relief Valve Port	Suggested HP Range	Approx. Weight (lbs)	Belt Guard for BBF Series		Boot Kit Part Number
				A	B	C				Part No.	Approx. lbs	
2"	2"	135	BBF-200	12.02	27.50	23.50	2 1/2"	5 - 20	130	DL-200	20	BK200
2 1/2"	2 1/2"	195	BBF-250	12.02	27.50	23.50	2 1/2"	5 - 20	130	DL-200	20	BK200
3"	3"	300	BBF-300	15.19	35.00	28.00	2"	10 - 50	180	DL-300	23	BK300
4"	4"	520	BBF-400	15.19	35.00	28.00	2"	10 - 50	180	DL-300	23	BK400
6"	6" Flg	1100	BBF-600F	17.76	39.50	38.45	3"	20 - 60	398	DL-600	28	BK600

Optional Accessories



Belt guard



Boot kit (includes flexible boot and 2 clamps).

Learn More

For more information about Solberg products and finding the right solutions for your equipment needs, visit us at SolbergMfg.com.

Contact Us

solbergmfg.com/locations

