


SPARTAN
SCIENTIFIC

6200 Series Valves

Part no. **6200-650-AAC7C-A**Part no. **6200-650-AAC7B-A**

6200 series valves are 2-way, normally closed, direct acting valves. The engineered composite body material and other wetted materials are suitable for potable water applications.

Features

- Direct Acting Operator
- Glass reinforced Nylon body
- Port sizes 1/8, 1/4 and 3/8 inch NPT
- 2-way, 2-position normally closed operation
- 24 VDC or 120 VAC (other voltage coils available)



See our website
www.AutomationDirect.com
for a variety of cable options.

6100 Series Solenoid Valves

Part No.	Price	Ports	Cv	Max Pressure	Operating Voltage	Connection	Weight (lbs)	Drawing Link	Vendor Specs	Vendor Application and Install Guide
6200-650-AAC7C-A	\$55.00	3/8in female NPT inlet(s), 3/8in female NPT outlet(s)	0.31	250 psi	120VAC	18mm DIN style wiring plug	0.30	PDF	PDF	PDF
6200-650-AAC3C-A	\$55.00			150 psi	24VDC		0.30	PDF		
6200-660-AAA7C-A	\$55.00	1/8in female NPT inlet(s), 1/8in female NPT outlet(s)	0.52	75 psi	120VAC		0.30	PDF		
6200-660-AAA3C-A	\$55.00			80 psi	24VDC		0.30	PDF		
6200-670-AAB7C-A	\$55.00	1/4in female NPT inlet(s), 1/4in female NPT outlet(s)	0.61	50 psi	120VAC		0.30	PDF		
6200-670-AAB3C-A	\$55.00				24VDC		0.30	PDF		
6200-680-AAC7C-A	\$55.00	3/8in female NPT inlet(s), 3/8in female NPT outlet(s)	0.72	40 psi	120VAC		0.30	PDF		
6200-680-AAC3C-A	\$55.00			30 psi	24VDC		0.30	PDF		
6200-650-AAC7B-A	\$54.00	3/8in female NPT inlet(s), 3/8in female NPT outlet(s)	0.31	250 psi	120VAC	18in pigtail (PVC 22AWG multi-strand copper wire 300 Volt)	0.30	PDF		
6200-650-AAC3B-A	\$54.00			150 psi	24VDC		0.30	PDF		
6200-660-AAA7B-A	\$54.00	1/8in female NPT inlet(s), 1/8in female NPT outlet(s)	0.52	75 psi	120VAC		0.30	PDF		
6200-660-AAA3B-A	\$54.00			80 psi	24VDC		0.30	PDF		
6200-670-AAB7B-A	\$54.00	1/4in female NPT inlet(s), 1/4in female NPT outlet(s)	0.61	50 psi	120VAC		0.30	PDF		
6200-670-AAB3B-A	\$54.00				24VDC		0.30	PDF		
6200-680-AAC7B-A	\$54.00	3/8in female NPT inlet(s), 3/8in female NPT outlet(s)	0.72	40 psi	120VAC		0.30	PDF		
6200-680-AAC3B-A	\$54.00			30 psi	24VDC		0.30	PDF		


SPARTAN
SCIENTIFIC

6100, 6200, 6222 Series Valve Accessories

- Spartan Series Replacement Coils for use with 6100, 6200 and 6222 Series Valves
- A variety of voltages are available for use in any valve: 12VDC, 24VDC, 24VAC, 120VAC and 220VAC
- Coils offered with either 18mm DIN plug or 18in pigtail (PVC 22AWG multistrand copper wire 300 Volt)

Part no. **4A000-01201-A**Part no. **4A001-01201-A**

See our website
www.AutomationDirect.com
for a variety of cable options.

6100, 6200, 6222 Series Valve Accessories				
Part No.	Price	Description	Weight (lbs)	Drawing Link
<u>4A000-01201-A</u>	\$28.00	Spartan solenoid coil, 12 VDC, 10W, 18mm DIN style wiring plug. For use with 6100, 6200 and 6222 series Spartan valves.	<u>0.30</u>	<u>PDF</u>
<u>4A000-02401-A</u>	\$28.00	Spartan solenoid coil, 24 VDC, 10W, 18mm DIN style wiring plug. For use with 6100, 6200 and 6222 series Spartan valves.	<u>0.30</u>	<u>PDF</u>
<u>4A000-02411-A</u>	\$28.00	Spartan solenoid coil, 24 VAC, 11.5 VA, 18mm DIN style wiring plug. For use with 6100, 6200 and 6222 series Spartan valves.	<u>0.30</u>	<u>PDF</u>
<u>4A000-12011-A</u>	\$28.00	Spartan solenoid coil, 120 VAC, 11.5 VA, 18mm DIN style wiring plug. For use with 6100, 6200 and 6222 series Spartan valves.	<u>0.30</u>	<u>PDF</u>
<u>4A000-22011-A</u>	\$28.00	Spartan solenoid coil, 220 VAC, 11.5 VA, 18mm DIN style wiring plug. For use with 6100, 6200 and 6222 series Spartan valves.	<u>0.30</u>	<u>PDF</u>
<u>4A001-01201-A</u>	\$37.00	Spartan solenoid coil, 12 VDC, 10W, 18in 22AWG pigtail. For use with 6100, 6200 and 6222 series Spartan valves.	<u>0.30</u>	<u>PDF</u>
<u>4A001-02401-A</u>	\$37.00	Spartan solenoid coil, 24 VDC, 10W, 18mm DIN style wiring plug. For use with 6100, 6200 and 6222 series Spartan valves.	<u>0.30</u>	<u>PDF</u>
<u>4A001-02411-A</u>	\$37.00	Spartan solenoid coil, 24 VAC, 11.5 VA, 18mm DIN style wiring plug. For use with 6100, 6200 and 6222 series Spartan valves.	<u>0.30</u>	<u>PDF</u>
<u>4A001-12011-A</u>	\$37.00	Spartan solenoid coil, 120 VAC, 11.5 VA, 18mm DIN style wiring plug. For use with 6100, 6200 and 6222 series Spartan valves.	<u>0.30</u>	<u>PDF</u>
<u>4A001-22011-A</u>	\$37.00	Spartan solenoid coil, 220 VAC, 11.5 VA, 18mm DIN style wiring plug. For use with 6100, 6200 and 6222 series Spartan valves.	<u>0.30</u>	<u>PDF</u>