



The **ONLY** industry manufacturer of the **complete line of OEM CAMSTAT®** made in our Allenwood, New Jersey facility.



FAL SERIES
UNIVERSAL FAN & LIMIT CONTROLS

- Adjustable fan "OFF" setting
- Adjustable fan differential setting
- Adjustable Limit Temperature

| SUPCO® P/N | A1® # | L (in.) | Fan Off Temp °F | Fan Diff. °F | Limit Temp °F |
|----------------|-------|---------|-----------------|--------------|---------------|
| FAL3C05TD120A | FF558 | 3" | 90-120 | 25-50 | 150-250 |
| FAL7C05TD120A | FF559 | 7" | 90-120 | 25-50 | 150-250 |
| FAL7C20BT120AB | FF594 | 7" | 90-120 | 25-50 | 150-250 |

Limit Differential of 30 °F for all



FALTS SERIES
FAN AND LIMIT CONTROLS W/ HEAT ASSIST

- SPST Switch
- Adjustable Limit Temperature
- Pilot Duty: 40 VA @ 30 VAC & 120 VAC

| SUPCO® P/N | A1® # | L (in.) | Fan Off Temp °F | Limit Temp °F |
|------------------|-------|---------|-----------------|---------------|
| FALTS57C05T120A | FF560 | 7" | 90-120 | 150-250 |
| FALTS57C65T120A | FF561 | 7" | 90-120 | 150-250 |
| FALTS57C13BT120A | FF591 | 7" | 90-120 | 150-250 |

Limit Differential of 30 oF for all

*Length with shield



S106 SERIES
TIME DELAY RELAYS

- SPST or SPDT
- Delay on/ off timing

Time Delay

| SUPCO® P/N | A1® # | On (sec.) | Off (sec.) |
|--------------|-------|-----------|------------|
| S1061A4575C | FF582 | 30-50 | 60-90 |
| S1061A5040C | FF583 | 45-55 | 30-50 |
| S1061A40100C | FF584 | 35-45 | 80-110 |
| S1061A5560C | FF585 | 50-60 | 45-75 |
| S1061B6545C* | FF586 | 60-70 | 45-75 |

*SPDT. All others are SPST



L59 SERIES
LIMIT CONTROLS

- SPDT Switch
- User Temperature Adjustment

| SUPCO® P/N | A1® # | L (in.) | Fan Off Temp °F |
|------------|-------|---------|-----------------|
| L593BA | FF568 | 3" | 120-250 |
| L597BA | FF569 | 7" | 120-250 |

Fixed Differential of 30 oF for both

VISIT SUPCO.COM TO VIEW THE FULL LINE

REPLACES 99% OF ALL HUMIDIFIER SOLENOIDS IN THE FIELD

UHS UNIVERSAL HUMIDIFIER SOLENOID VALVE REPLACEMENT KITS

| SUPCO® Part No. | Volts | Can Replace |
|-----------------|-------|---|
| SUHS24 | 24V | Aprilaire® 4040, General® 990-53, Honeywell® 320016939-002, Skuttle® A01-0814-148 |
| UHS120 | 120V | Aprilaire® 4005, General® 990-52 |

- Each kit includes solenoid valve, mounting bracket and all fittings to remove and replace the existing solenoid valve
- Easy "wrench-in" installation
- Adjustable water flow valve
- Economically priced compared to OEM versions



34 800.333.9125