



Family

**Catalog Number:** BVIRB-U232  
**Product ID:** 7TAA292610R0096  
**UPC Number:** 78620995032  
**EAN Number:** 07630030215063  
**Status:** Active

PMAFIX Black Female Thread Adapter with UNEF Threads, Material - Polyamide 6, Thread Size - 15/16 Inch - 20, Nominal Width/Conduit Size - 12

- Very high impact resistance
- Vibration proof connection to PMAFLEX conduits
- High conduit pull-out strength
- Very good chemical properties
- Free from halogens and cadmium
- Fits both conduit profiles - Fine (T) and coarse (G)

### Header

3D Model Available on Website

### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	PMA
Type	Adapters-Female
Application	For Use In Machine, Vehicle and Traction Building
Size	NW12
Material	Polyamide 6
Insulation Class	IP68
Color	Black
Connection	15/16 Inch
Temperature Rating	-40 Degrees C to 105 Degrees C; Short Term to 160 Degrees C

### European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	16mm
Degree of protection (IP)	IP68
Model	Straight
Revolving thread	N
Construction type	External thread
Type of connection	Snap connection
Thread type	UNEF
Thread connection size	Other
Thread material	Polyamide
Thread length	4.5mm
Total length	49mm
Material	Polyamide
Material sealing	No sealing
Colour	Black
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UR	Y
Approved in combination with protective conduit DIN EN 61386-23	N
	N

Approved in combination with protective  
conduit Lloyd's Register

Operating temperature	-40 - +105°C
-----------------------	--------------

### Packaging

Inner Quantity	50
Outer Quantity	200
Outer Dimensions (inches)	15.748x11.811x7.874
Weight Uom	0.27 lbs. Each

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com