

# Product data sheet

Specifications

**SQUARE** D



Switch, reversing drum, 2 HP at 230 VAC single phase, 2 HP at 575 VAC polyphase, handle operated, NEMA 1 enclosure

2601AG2

**Product availability : Stock - Normally stocked in distribution facility**

## Main

<b>Product</b>	Reversing Drum Switch
<b>Enclosure Rating</b>	NEMA 1
<b>Horsepower</b>	1.5 hp 115 V AC, 1 phase 2 hp 230 V AC, 1 phase 2 hp 200 V AC, 3 phase 2 hp 230 V AC, 3 phase 2 hp 460 V AC, 3 phase 2 hp 575 V AC, 3 phase 0.25 hp 115 V DC 0.25 hp 230 V DC
<b>Maximum Rated Voltage</b>	600 V AC 250 V DC
<b>Number of Poles</b>	3P

## Complementary

<b>Certifications</b>	UL Listed CSA
<b>Electrical Connection</b>	Screw-clamp terminals
<b>Type</b>	A
<b>Width</b>	2.68 in (68.07 mm)
<b>Height</b>	5.38 in (136.65 mm)
<b>Depth</b>	4.61 in (117.09 mm)
<b>Product weight</b>	1.34 lb(US) (0.61 kg)

## Ordering and shipping details

<b>Category</b>	21116-2601
<b>Discount Schedule</b>	CP1
<b>GTIN</b>	785901555414
<b>Returnability</b>	Yes
<b>Country of origin</b>	MX

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1

<b>Package 1 Height</b>	4.69 in (11.9 cm)
<b>Package 1 Width</b>	5.59 in (14.2 cm)
<b>Package 1 Length</b>	7.01 in (17.8 cm)
<b>Package 1 Weight</b>	20.00 oz (567.0 g)


## Offer Sustainability

<b>California proposition 65</b>	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>EU RoHS Directive</b>	Not compliant
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------


**Approximate Dimensions**




**Connections and Wiring Diagrams**

---

Internal Switching



Three-Phase Wiring Diagram



**Recommended replacement(s)**