

Product data sheet

Specifications

SQUARE D

Green Premium™



Tandem mini circuit breaker, QO, 2 x 1 pole at 20A, 120/240VAC, 10kA, plug in mount

QO2020

Product availability : Stock - Normally stocked in distribution facility

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	20 A
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Tandem
Ratings	HACR rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	10 kA 120/240 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 14...AWG 8 copper or aluminium
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	3.23 in (82 mm)
Width	0.75 in (19 mm)
Depth	2.91 in (74 mm)
Net Weight	0.30 lb(US) (0.136 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00181-REPLCMNT TANDEMS - DO NOT NEGOTIATE
Discount Schedule	DE2A
GTIN	785901400943
Returnability	Yes

Country of origin	MX
-------------------	----

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.30 in (8.382 cm)
Package 1 Width	0.80 in (2.032 cm)
Package 1 Length	3.30 in (8.382 cm)
Package 1 Weight	4.80 oz (136.078 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	3.80 in (9.652 cm)
Package 2 Width	2.70 in (6.858 cm)
Package 2 Length	7.60 in (19.304 cm)
Package 2 Weight	3.29 lb(US) (1.492 kg)
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	8.20 in (20.828 cm)
Package 3 Width	8.10 in (20.574 cm)
Package 3 Length	19.80 in (50.292 cm)
Package 3 Weight	34.35 lb(US) (15.581 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
RoHS exemption information	Yes
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)