



Actual

Catalog Number: XR90G-36BR.30
Product ID: 7TAA292240R0323
UPC Number: 78620962251
EAN Number: 07630030282195
Status: Active

Very Flexible, Medium Duty Three Layer Corrugated Conduit - Conduit Size NW/Metric 36/40, Outer Layer Black, Intermediate Layer Yellow, Inner Layer Red, 30 Meters

North American Specifications (UNSPSC)

| | |
|-------------|-------------------------------------|
| UNSPSC | 39131706 Electrical conduit |
| IGCC | 5535 Electrical conduit |
| Brand Name | PMA |
| Type | Medium Wall Conduit |
| Application | In Robotics and Automation Industry |
| Trade Size | NW36 |
| Length | 30 m |
| Radius | 180 Millimeters |
| Flexibility | Very Flexible |
| Material | Polyamide 12 |
| Color | Red, Yellow, Black |

European Specifications (ETIM)

| | |
|--|----------------------------------|
| ETIM | EC001175 Corrugated plastic hose |
| Nominal diameter | 40mm |
| Outer diameter | 42.2mm |
| Inner diameter | 36.8mm |
| Material | Polyamide 12 |
| Compressive strength | 130N |
| Operating temperature | -40 - +95°C |
| Fire resistance in accordance with UL94 | HB |
| UV resistant | Y |
| Colour | Black |
| Sheathing material | Polyamide |
| Bending strength | Flexible |
| Lengthwise slotted | N |
| Closable (two-part) | N |
| Halogen free | Y |
| Approved according to DIN EN 61386-23 | N |
| Approved according to UR | N |
| Approved according to CSA | N |
| Approved according to LUL/British Standard | N |
| Approved according to Lloyd's Register TA | N |
| Approved according to UTAC | N |
| Approved according to DIN 5510 | N |
| Approved according to NF F 16-101 | N |

Packaging

| | |
|---------------------------|----------------------|
| Inner Quantity | 1 |
| Outer Quantity | 6 |
| Outer Dimensions (inches) | 47.244x31.496x30.709 |
| Weight Uom | 21.32 lbs. Each |

Documents / Support Tools

Video US Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

T&B Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com