



Wera Ratchets

BE A TOOL REBEL



Zyklop Metal Ratchet



Small return angle

The fine 72 tooth ratchet mechanism has a low return angle of 5°. This short stroke allows fast and precise work in small spaces.



Extremely slim Long leverage

Forged, chrome-molybdenum steel ratchet has no torque limitation and is designed to fit in tight areas.



Secure socket lock mechanism

The ball lock holds sockets and attachments securely, ensuring safe operation. To release the socket simply press the release button.

Wera Metal Ratchets and Ratchet Sets			
Part Number	Description	Pcs/Pkg	Price
05004004055	Wera Zyklop Metal ratchet, switch lever, 1/4 inch drive, 5 degree return angle, all metal construction, secure socket lock mechanism.	1	\$49.00
05004034055	Wera Zyklop Metal ratchet, switch lever, 3/8 inch drive, 5 degree return angle, all metal construction, secure socket lock mechanism.	1	\$56.00
05004064055	Wera Zyklop Metal ratchet, switch lever, 1/2 inch drive, 5 degree return angle, all metal construction, secure socket lock mechanism.	1	\$63.00



Switch Lever

Switch lever for convenient change of direction.



Zyklop Metal Ratchet and Socket Sets



1/2 inch Drive Imperial and Metric Ratchet Sets



1/2 inch Drive Metal Ratchet Sets		
Part Number	Description	Price
05004081055	Wera socket set with Zyklop Metal switch lever ratchet, 1/2 inch drive, SAE. 28 pieces. Durable cloth pouch included. Manufacturer part number 004081.	\$214.00
05004078055	Wera socket set with Zyklop Metal switch lever ratchet, 1/2 inch drive, metric. 28 pieces. Durable cloth pouch included. Manufacturer part number 004078.	\$214.00

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect.



Wera socket set with Zyklop Metal switch lever ratchet, 1/2 inch drive, SAE, 28 pieces. Includes the pieces listed in the table below.



Wera socket set with Zyklop Metal switch lever ratchet, 1/2 inch drive, metric, 28 pieces. Includes the pieces listed in the table below.

05004081055 Contents		
	1/2 Zyklop Metal ratchet	
	6-point socket, 37mm long	3/8, 7/16, 1/2, 9/16, 19/32, 5/8, 11/16, 3/4, 25/32, 13/16
	Extension	1/2 x 250
	Wobble Extension	1/2 x 52
	Bit adaptor	1/2 x 5/16 x 50
	Hex-Plus bit, 30mm long	7/32, 1/4, 5/16, 3/8
	Phillips bit, 32mm long	PH2, PH3
	Torx® bit, 35mm long	TX20, TX25, TX27, TX30, TX40, TX45, TX50, TX55

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.

05004078055 Contents		
	1/2 Zyklop Metal ratchet	
	6-point socket, 37mm long	10, 11, 12, 13, 14, 15, 16, 17, 18, 19
	Extension	1/2 x 250
	Wobble Extension	1/2 x 52
	Bit adaptor	1/2 x 5/16 x 50
	Hex-Plus bit, 30mm long	5, 6, 8, 10
	Phillips bit, 32mm long	PH2, PH3
	Torx® bit, 35mm long	TX20, TX25, TX27, TX30, TX40, TX45, TX50, TX55

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.