



# Screwdrivers



## Anti-Rolloff

The hexagonal non-roll feature prevents any rolling away at the workplace.



## Laser Tip

Laser treatment creates a microrough surface on the tip of the blade. The drive end literally bites into the head of the screw. The advantages: less slipping, fewer scratches, higher torque transfer and less screwdriving effort.



## Handle Markings

Handle markings include a screw symbol and the size of the tip to help you find the right screwdriver in your tool bag or at the workplace.



## Kraftform Ergonomics

The Kraftform handle has been designed to fit snugly in your hand, making blisters and calluses a thing of the past even after long-term use. The hard materials used for the handle promote fast grip adjustments and prevent the skin from sticking to the handle. The softer, anti-slip zones facilitate zero-loss transfer of high forces. This is an unbeatable combination! Work is done with a flick of the wrist!



## Hex Plus Profile

The problem with hexagon socket screws is the easily "rounded" screw recess. This is caused by the sharp edges of the tool pressing against the inside of the screw profile. Gradual wear eventually grinds and destroys the head of the screw. Wera's Hex-Plus tools provide more contact surface inside the screw profile, which reduces the notching effect and ultimately the deformation of the screw. Hex-Plus tools can also transfer up to 20% more TORQUE.



## Extra Durable (Black Point)

The Wera Black Point tip and a refined hardening process guarantee a long service life and increased corrosion protection.



# Wera Screwdrivers



## Standard Screwdrivers

Kraftform Plus screwdrivers transfer more torque with less effort, relieving physical stress even during intensive use. Combined with other practical and technical product advantages, such as the lasertip for a secure fit in the screw, and greater cam-out protection, Kraftform screwdrivers are the perfect choice for manual work.



Standard Screwdrivers		
Part Number	Description	Price
<b><u>TW-SD-SET-1</u></b>	Wera screwdriver set. 6 pieces. Wall mount rack included. Manufacturer part number 105650.	\$36.00
<b><u>TW-SD-SL-1</u></b>	Wera flat (slotted) screwdriver, 0.5 mm (0.02 inch) thick x 3mm (0.12 inch) wide x 80mm (3.15 inch) long blade. Manufacturer part number 110001.	\$5.75
<b><u>TW-SD-SL-2</u></b>	Wera flat (slotted) screwdriver, 0.8 mm (0.03 inch) thick x 4mm (0.16 inch) wide x 100mm (3.94 inch) long blade with laser etched non-slip tip. Manufacturer part number 110004.	\$4.50
<b><u>TW-SD-SL-3</u></b>	Wera flat (slotted) screwdriver, 1mm (0.04 inch) thick x 5.5 mm (0.22 inch) wide x 125mm (4.92 inch) long blade with laser etched non-slip tip. Manufacturer part number 110007.	\$7.50
<b><u>TW-SD-SL-4</u></b>	Wera flat (slotted) screwdriver, 1.2 mm (0.05 inch) thick x 6.5 mm (0.26 inch) wide x 150mm (5.91 inch) long blade with laser etched non-slip tip. Manufacturer part number 110010.	\$10.50
<b><u>TW-SD-PH-1</u></b>	Wera Phillips screwdriver, #1 x 80mm (3.15 inch) long blade with laser etched non-slip tip. Manufacturer part number 008710.	\$6.75
<b><u>TW-SD-PH-2</u></b>	Wera Phillips screwdriver, #2 x 100mm (3.94 inch) long blade with laser etched non-slip tip. Manufacturer part number 008720.	\$9.50
<b><u>TW-SD-PH-3*</u></b>	Wera Phillips screwdriver, #0 x 60mm (2.36 inch) long blade. Manufacturer part number 008705.	\$5.25
<b><u>05138262055*</u></b>	Wera tamper-proof TORX screwdriver, TX20 x 100mm (3.94 inch) long blade. Manufacturer part number 138262.	\$8.25

\* TW-SD-PH-3 and 05138262055 have hardened Black Point tip instead of laser-etched non-slip tip.



**TW-SD-PH-1**



**TW-SD-SET-1**



Extra Long Screwdrivers		
Part Number	Description	Price
<b><u>05008715055</u></b>	Wera Phillips extra long screwdriver, #1 x 300mm (11.81 inch) long blade. Manufacturer part number 008715.	\$8.50
<b><u>05008730055</u></b>	Wera Phillips extra long screwdriver, #2 x 300mm (11.81 inch) long blade. Manufacturer part number 008730.	\$11.00
<b><u>05008027055</u></b>	Wera flat (slotted) extra long screwdriver, 0.8mm (0.03 inch) thick x 4mm (0.16 inch) wide x 300mm (11.81 inch) long blade. Manufacturer part number 008027.	\$9.00
<b><u>05008060055</u></b>	Wera flat (slotted) extra long screwdriver, 1mm (0.04 inch) thick x 5.5mm (0.22 inch) wide x 300mm (11.81 inch) long blade. Manufacturer part number 008060.	\$10.00

TW-SD-SET-1 Contents		
	Slotted	3*, 4, 5.5, 6.5 mm
	Phillips	PH1, PH2

Note:\* 3mm screwdriver does not have laser-etched non-slip tip.



**05008027055**