



# Screwdrivers



## Anti-Rolloff

The hexagonal non-roll feature prevents any rolling away at the workplace.



## Laser Tip

Laser treatment creates a microrough surface on the tip of the blade. The drive end literally bites into the head of the screw. The advantages: less slipping, fewer scratches, higher torque transfer and less screwdriving effort.



## Handle Markings

Handle markings include a screw symbol and the size of the tip to help you find the right screwdriver in your tool bag or at the workplace.



## Kraftform Ergonomics

The Kraftform handle has been designed to fit snugly in your hand, making blisters and calluses a thing of the past even after long-term use. The hard materials used for the handle promote fast grip adjustments and prevent the skin from sticking to the handle. The softer, anti-slip zones facilitate zero-loss transfer of high forces. This is an unbeatable combination! Work is done with a flick of the wrist!



## Hex Plus Profile

The problem with hexagon socket screws is the easily "rounded" screw recess. This is caused by the sharp edges of the tool pressing against the inside of the screw profile. Gradual wear eventually grinds and destroys the head of the screw. Wera's Hex-Plus tools provide more contact surface inside the screw profile, which reduces the notching effect and ultimately the deformation of the screw. Hex-Plus tools can also transfer up to 20% more TORQUE.



## Extra Durable (Black Point)

The Wera Black Point tip and a refined hardening process guarantee a long service life and increased corrosion protection.





# Bit Drivers and Bits



RAPIDAPTOR  
TECHNOLOGY



Single hand quick release.



## Rapid-out

Simply push the sleeve forward to change the bit.



## BiTorsion

BiTorsion bits are absolutely premium products. They have a softer BiTorsion zone which reduces the hardness of the shaft by about 20% in comparison to the drive tip. This means that the peak loads that cause bit breakage and premature wear are absorbed in this zone – something which enhances the service life of the bits.




IMPACT  
PROOF



## Impact Proof

Impaktor bits are needed when a strong power tool is used. Impact bits were specifically developed to withstand high power tool forces.



## Diamond coated bits

Today, the Wera diamond bit – manufactured with the technology specifically developed by Wera – still sets the standard in terms of resilience and functionality. Wera bits with a diamond coating ensure a secure fit of the bit in the screw head.

# Wera Screwdriver Bit Sets



## Screwdriver Bit Sets


Wera bits have been designed for demanding applications in trade and industry. They are able to transfer high torque loads, are safe to use and extremely durable.

| Driver Bit Adapter          |   |         |
|-----------------------------|---|---------|
| Part Number                 | Description   | Price   |
| <b><u>TW-DB-ADT-MAG</u></b> | Wera Rapidaptor driver bit adapter, 1/4 inch drive, overall length 2-1/4 inch, ring magnet. Manufacturer part number: 052490. | \$21.50 |

Note: Bit-holders are warranted against manufacturer defect only.



**TW-DB-ADT-MAG**



## Telescopic Blade

When the unique telescopic blade is lowered into the handle, fast, easy screw-driving action is possible, even in the tightest spots! By pushing the clamping sleeve, the telescopic blade can be extended out of the handle and the compact tool becomes a full-sized screwdriver. If the clamping sleeve is pushed again the telescopic blade can be taken out of the handle, and be used as a machine bit adapter.



| Screwdriver Bit Set         |  |         |
|-----------------------------|--|---------|
| Part Number                 | Description  | Price   |
| <b><u>TW-DB-SET-SD1</u></b> | Wera Kraffform Kompact driver bit set with screwdriver, 1/4 inch drive. 8 pieces. Durable cloth pouch included. Manufacturer part number 051024. | \$45.00 |

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.



**TW-DB-SET-SD1**

| TW-DB-SET-SD1 Contents |   |                                 |
|------------------------|---|---------------------------------|
|                        | Kraffform Kompact bit-holding bayonet screwdriver |                                 |
|                        | 1/4 Rapidaptor bit holder                         | 1/4 x 50                        |
|                        | Slotted bit, 25mm long                            | 0.6 x 4.5, 1.0 x 5.5, 1.2 x 6.5 |
|                        | Phillips bit, 25mm long                           | PH1, PH2, PH3                   |

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.

# Wera Driver Bit Sets



## Bits, Bitholding Screwdriver and L-Keys in One Tool Set

This 52-piece set packs maximum screw-driving utility into a compact, lightweight set protected by an extremely robust folding textile box:

- BiTorsion bits for long service life
- Impaktor bits for extreme conditions
- Chrome-plated Hex-Plus L-keys with ball-end hex on long arm
- One Rapidaptor bit holder for quick, one-handed bit changes
- One Kraftform Kompact bit-holding screwdriver for that ergonomic Kraftform feel

| Impact Driver Set  |  |          |
|--------------------|--|----------|
| Part Number        | Description  | Price    |
| <b>05057460055</b> | Wera Kraftform Kompact series driver set with screwdriver, 1/4inch hex socket drive, metric. 52 pieces. Includes Kraftform Kompact bitholding screwdriver and durable cloth pouch. Manufacturer part number: 057460. | \$135.00 |

**Note: Screwdriver bits, bit-holders and L-keys are warranted against manufacturer defect only.**



05057460055



| 05057460055 Contents |  |  |
|----------------------|--|--|
|                      | 1/4 Kraftform Kompact bitholding screwdriver |  |
|                      | 1/4 Rapidator holder                         | 1/4 x 50   |
|                      | BiTorsion Phillips, 25mm long                | (2) PH1, (4) PH2, (2) PH3  |
|                      | Impaktor Phillips bit, 50mm long             | (2) PH2, PH3   |
|                      | BiTorsion Pozidriv® bits, 25mm long          | (2) PZ1, (4) PZ2, (2) PZ3  |
|                      | Impaktor Pozidriv® bits, 50mm long           | (2) PZ2, PZ3   |
|                      | BiTorsion Torx® bits                         | (2) TX10, (2) TX15, (3) TX20, (2) TX25, (2) TX30, TX40                           |
|                      | Impaktor Torx® bits, 50mm long               | TX25, TX30, TX40   |
|                      | BiTorsion® slotted bit, 25mm long            | 0.8 x 5.5, 1.0 x 5.5   |
|                      | Impaktor Hex-Plus bit, 50mm long             | 4.0, 5.0, 6.0  |
|                      | Hex Plus L-key                               | 1.5 x 50, 2.0 x 56, 2.5 x 63, 3.0 x 71, 4.0 x 80, 5.0 x 90, 6.0 x 100, 8.0 x 112 |

**Note: Fractional dimensions are in inches.  
Whole and decimal dimensions are in millimeters.**



# Wera Screwdriver Bits

## Screwdriver Bits

Wera bits have been designed for demanding applications in trade and industry. They are able to transfer high torque loads, are safe to use and extremely durable.

| Screwdriver Bits                  |   |         |         |
|-----------------------------------|---|---------|---------|
| Part Number                       | Description   | Pcs/Pkg | Price   |
| <u><a href="#">TW-DB-PH-1</a></u> | Wera driver bit, Phillips #1 x 70mm (2.75 inch) long, 1/4 inch hex drive, 10 bits per pack. Manufacturer part number 059755.  | 10      | \$14.00 |
| <u><a href="#">TW-DB-PH-2</a></u> | Wera driver bit, Phillips #2 x 70mm (2.75 inch) long, 1/4 inch hex drive, 10 bits per pack. Manufacturer part number 059770.  | 10      | \$13.00 |
| <u><a href="#">TW-DB-SL-1</a></u> | Wera driver bit, flat (slotted), 0.5mm (0.02 inch) thick x 3mm (0.12 inch) wide x 50mm (1.97 inch) long, 1/4 inch hex drive, 10 bits per pack. Manufacturer part number 059305. | 10      | \$33.00 |

Note: Screwdriver bits are warranted against manufacturer defect only.



[TW-DB-SL-1](#)



[TW-DB-PH-1](#)

# Wera Zyklop Mini Bit Ratchet Sets



| Zyklop Mini Bit Ratchet Sets |  |          |
|------------------------------|--|----------|
| Part Number                  | Description  | Price    |
| <b>05073220055</b>           | Wera Tool-Check driver bit and socket set with Zyklop Mini bit ratchet, 1/4 inch drive, metric. 38 pieces. Plastic case included. Manufacturer part number 073220. | \$108.00 |
| <b>TW-DB-SET-28R</b>         | Wera Bit-Check driver bit set with Zyklop Mini bit ratchet, 1/4 inch drive, SAE. 31 pieces. Plastic case included. Manufacturer part number 346293.                | \$81.00  |

Note: Screwdriver bits are warranted against manufacturer defect.



Wera Tool-Check driver bit and socket set with Zyklop Mini bit ratchet, 1/4 inch drive, SAE, 38 pieces. Includes the pieces listed in the table below.

| 05073220055 Contents    |                                   |                                     |
|-------------------------|-----------------------------------|-------------------------------------|
| Zyklop Mini bit ratchet |                                   |                                     |
|                         | Rapidaptor bit holder             | 1/4 x 50                            |
|                         | 1/4 socket adaptor                | 1/4 x 25                            |
|                         | Slotted                           | 1.0 x 5.5 x 25                      |
|                         | Hex-Plus bit, 25mm long           | 3, 4, 5, 6, 8                       |
|                         | Phillips bit, 25mm long           | (2) PH1, (3) PH2, PH3               |
|                         | Torx® bit, 25mm long              | TX10, TX15, TX20, TX25, TX30, TX40  |
|                         | Tamper-proof Torx® bit, 25mm long | TX10, TX15, TX20, TX25, TX30        |
|                         | Posidriv® bit, 25mm long          | PZ1, (3) PZ2, PZ3                   |
|                         | 6-point socket                    | 5.5, 6.0, 7.0, 8.0 10.0, 12.0, 13.0 |



Wera Bit-Check driver bit set with Zyklop Mini bit ratchet, 1/4 inch drive, SAE, 31 pieces. Includes the pieces listed in the table below.

| TW-DB-SET-28R Contents  |                                   |                                    |
|-------------------------|-----------------------------------|------------------------------------|
| Zyklop Mini bit ratchet |                                   |                                    |
|                         | 1/4 Rapidaptor bit holder         | 1/4 x 50                           |
|                         | 1/4 socket adaptor                | 1/4 x 25                           |
|                         | Phillips bit, 25mm long           | (2) PH1, (3) PH2, PH3              |
|                         | Torx® bit, 25mm long              | TX10, TX15, TX20, TX25, TX30, TX40 |
|                         | Tamper-proof Torx® bit, 25mm long | TX10, TX15, TX20, TX25, TX30       |
|                         | Slotted bit                       | 1.0 x 5.5 x 25                     |
|                         | Hex-Plus bit, 25mm long           | 3/32, 1/8, 5/32, 3/16, 1/4         |
|                         | Square bit, 25mm long             | #1, (3) #2, #3                     |

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.