


PRO SERIES SERVICE FITTINGS

Compatible with Walkerdut Pro Series only


Walkerdut Pro Series Flush Brushed Aluminum Flanges Ordering Information

828DLRAL Brushed Aluminum Single Locking Receptacle Cover Plate



Single flip lid cover for 20A or 30A single locking receptacles. Device opening is 2 5/8" (67mm). For use with maximum female locking device of 1.58" diameter, and maximum male plug face of 2.25" diameter.

828GFITCAL Brushed Aluminum GFI Cover Plate




May be used with Activate and Ortronics® Connectivity Systems in conjunction with 817, 827, and 837 Series flanges.

NOTE: Brass covers and flanges are not interchangeable with aluminum or nonmetallic covers and flanges.

Nonmetallic covers are interchangeable with aluminum flanges.


818TCAL One-Gang Brushed Aluminum Combination Carpet & Tile Flange



Accepts Ortronics® MAB6TJ TracJack and MAB3S2 Series II bezels, Activate CM-MAB bezel, and Wiremold Open System inserts, all sold separately.


NOTE: Brushed aluminum flange comes with a beveled edge.

828DPGFITCAL Brushed Aluminum Rectangular Cover Plate



Allows for mounting of a duplex style receptacle with a rectangular flip lid cover plate.


828TCAL Two-Gang Brushed Aluminum Combination Carpet & Tile Flange



Accepts Ortronics® MAB6TJ TracJack and MAB3S2 Series II adapters and Wiremold CM Series inserts, sold separately.

NOTE: Brushed aluminum flange comes with a beveled edge.


830CKTCAL Brushed Aluminum Cover Plate



Power or communication plate with 2" (51mm) and 1 1/4" (32mm) plugs.

NOTE: Acceptable for use with threaded conduit when passing through power cables.


838TCAL Three-Gang Brushed Aluminum Combination Carpet & Tile Flange



Accepts Ortronics® MAB6TJ TracJack and MAB3S2 Series II bezels, Activate CM-MAB bezel, and Wiremold Open Systems inserts, all sold separately.

NOTE: Brushed aluminum flange comes with a beveled edge.


830CKTCAL-1 Brushed Aluminum Cover Plate



Power or communication plate with 2" (51mm) and 1" (25mm) plugs.


NOTE: Acceptable for use with threaded conduit when passing through power cables.

830CKTCAL-3/4 Brushed Aluminum Cover Plate




Power or communication plate with 2" (51mm) and 3/4" (19.1mm) plugs.

830CKTCAL-1/2 Brushed Aluminum Cover Plate



Power or communication plate with 2" (51mm) and 1/2" (12.7mm) plugs.

828R-TCAL Brushed Aluminum Duplex Cover Plate




Flip lids. Can also be used with a 106 type communication bezel.

PRO SERIES SERVICE FITTINGS

Compatible with Walkerdut Pro Series only

Walkerdut Pro Series Powder-Coated Aluminum Cover Plates Ordering Information


One-Gang Powder-Coated Aluminum Combination Carpet and Tile Flange



PART NUMBERS:
817TCAL-BK (Black)
817TCAL-GY (Grey)
817TCAL-BS (Brass)
817TCAL-NK (Nickel)
817TCAL-BZ (Bronze)

Accepts Ortronics® MAB6TJ TracJack and MAB3S2 Series II adapters and Wiremold CM Series inserts, sold separately.


Three-Gang Powder-Coated Aluminum Combination Carpet and Tile Flange



PART NUMBERS:
827TCAL-BK (Black)
827TCAL-GY (Grey)
827TCAL-BS (Brass)
827TCAL-NK (Nickel)
827TCAL-BZ (Bronze)

Accepts Ortronics® MAB6TJ TracJack and MAB3S2 Series II adapters and Wiremold CM Series inserts, sold separately.


Three-Gang Powder-Coated Aluminum Combination Carpet and Tile Flange



PART NUMBERS:
837TCAL-BK (Black)
837TCAL-GY (Grey)
837TCAL-BS (Brass)
837TCAL-NK (Nickel)
837TCAL-BZ (Bronze)

Accepts Ortronics® MAB6TJ TracJack and MAB3S2 Series II adapters and Wiremold CM Series inserts, sold separately.

Powder-Coated Aluminum Duplex Cover Plate




PART NUMBERS:
828R-TCAL-BK (Black)
828R-TCAL-GY (Grey)
828R-TCAL-BS (Brass)
828R-TCAL-NK (Nickel)
828R-TCAL-BZ (Bronze)

Flip lids. Can also be used with a 106 type communication adapter.

NOTE: Acceptable for use with threaded conduit when passing through power cables.


Powder-Coated Aluminum Rectangular Cover Plate



PART NUMBERS:
828GFITCAL-BK (Black)
828GFITCAL-GY (Grey)
828GFITCAL-BS (Brass)
828GFITCAL-NK (Nickel)
828GFITCAL-BZ (Bronze)

Allows for mounting a duplex receptacle (Decorator or GFCI style) with a rectangular flip cover.


Powder-Coated Aluminum Cover Plate



PART NUMBERS:
829CKAL-1BK (Black)
829CKAL-1GY (Grey)
829CKAL-1BS (Brass)
829CKAL-1NK (Nickel)
829CKAL-1BZ (Bronze)

Power or communication plate with 2" (51mm) and 1" (25mm) plugs.

Powder-Coated Aluminum Cover Plate




PART NUMBERS:
829CKAL-3/4BK (Black)
829CKAL-3/4GY (Grey)
829CKAL-3/4BS (Brass)
829CKAL-3/4NK (Nickel)
829CKAL-3/4BZ (Bronze)

Power or communication plate with 2" (51mm) and 3/4" (19.1mm) plugs.

NOTE: Acceptable for use with threaded conduit when passing through power cables.

828MAAP A/V Adapter Plate



Sheet metal adapter plate that accepts two (2) Extron® Electronics MAAP style device plates, sold separately. For use with 828GFITC or 828GFITCAL cover plates, sold separately. For use with minimum 2 1/2" (64mm) preset depths.