


ALA3800 SERIES™ RACEWAY


ALA3800 Series Raceway Ordering Information

ALA3800B-10 Single Compartment Raceway Base




Satin Anodized finish. Nominal wall thickness of .078" (1.99mm). Packed four 10' (3m) lengths per carton.

ALA3810B1 Entrance End Fitting




For feeding raceway, has concentric 1/2" and 3/4" trade size knockouts.

ALAC-5 Raceway Cover




Satin Anodized finish. Nominal wall thickness of .078" (1.99mm). Packed eight 5' (1.50m) lengths per carton. ALAC-5 is compatible with ALA3800 and ALA4800 Series Raceways.

ALA3806 Cover Clip




Covers seam where lengths of raceway come together.

ALAWC Wire Clip




Holds conductors in place in long raceway runs. Snaps into grooves on base.

ALA3811 Flat Elbow




For making a 90° flat turn in a raceway run. Includes two ALA01 Couplings.

ALA01 Couplings




Joins lengths of inline ALA3800B-10 Raceway Base together.

ALA3815 Tee




For branch connections of two runs of ALA3800 Series Raceway. Includes three ALA01 Couplings.

ALA11RI Radiused Insert




A radiused insert for the ALA3811 and ALA4811 flat elbow to provide a bend radius of 2" (51mm) for Fiber Optic/ Category 5e installations. The insert is ideal for new and retrofit applications whether the cable installation is lay-in or pull-through.

ALA3817 Internal Elbow




For making a 90° internal turn in a raceway run. Includes two ALA01 Couplings.

ALA17/18RI Radiused Insert




A radiused insert for ALA3817, ALA4817, ALA3817N, ALA4817N, ALA3818, and ALA4818 fittings to provide a bend radius of 2" (51mm) for Fiber Optic/ Category 5e installations. The insert is ideal for new and retrofit applications whether the cable installation is lay-in or pull-through.

ALA3817N Inverted Internal Elbow




For connecting a vertical run of ALA3800 Series Raceway with a horizontal run with its cover facing up. Includes two ALA01 Couplings.

ALA3810B Blank End Fitting



Closes off open end of raceway.


ALA3818 External Elbow



For making a 90° external turn in a raceway run. Includes two ALA01 Couplings.

ALA3800 SERIES RACEWAY

Ordering Information




ALA3800 Series Aluminum Raceway System meets the demands of commercial spaces, directing power or communications services where required. The low-profile surface mounted raceway is easy to install and because of its two-piece design, wiring is always accessible.

Material: 6063 T6 Aluminum Alloy

Wall Thickness: 0.078" (1.99mm)


Anodized Finish Thickness: 0.004" (0.004mm)

ALAWC Wire Clip




Holds conductors in place in long runs of ALA3800 Series Raceway. Snaps into grooves on base.

ALA17A Internal Corner Coupling




Forms an internal 90° turn in a run of ALA3800 Series Raceway.

ALA01 Slide Coupling




Connects adjoining sections of ALA3800 Series Raceway base.

ALA3806 Cover Clip




Covers seams where sections of ALAC-5 Cover come together.

ALA09 Grounding Adapter



Connects equipment grounding conductor to ALA3800 Series Raceway.

ALA3810B Entrance End Cap



Closes off open ends of ALA3800 Series Raceway