



Representative



Family

Catalog Number: NKIS-M207
Product ID: 7TAA292400R0133
UPC Number: 78620996191
EAN Number: 07630030261626
Status: Active

PMAFIX Pro Black Female Thread Adapter with Metric Threads, Adapter Material - Polyamide 6, Thread Material - Nickel-Plated Brass, Thread Size - M20x1.5, Conduit Size NW - 17

- Very high impact resistance, even at very low temperatures
- High thread and system connection strengths
- Easy push-in assembly for maximum installation reliability
- Screwdriver required for dismantling, impeding unauthorized or accidental opening
- Space-saving dismantling
- Excellent conduit pull-out strength
- Fits both conduit profiles - Fine (T) and coarse (G)

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Brand Name	PMA
Type	Adapters-Female
Special Features	Adapters-Female
Application	For Applications with High Technical Requirements and In Most Demanding Climatic Conditions
Trade Size	NW17
Length	56 Millimeters
Material	Polyamide/Nylon 6
Connection	M20x1.5
Color	Black

European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	20mm
Degree of protection (IP)	Other
Model	Straight
Revolving thread	N
Construction type	External thread
Type of connection	Snap connection
Thread type	Metric
Thread connection size	M20 x 1.5
Thread material	Brass
Thread length	10.5mm
Total length	56mm
Material	Polyamide
Material sealing	No sealing
Colour	Black
Approved in combination with protective conduit CSA	N
	Y

Approved in combination with protective conduit UR	
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit Lloyd's Register	N
Operating temperature	-40 - +105°C

Packaging

Inner Quantity	50
Outer Quantity	150
Outer Dimensions (inches)	15.748x11.811x7.874
Weight Uom	0.08 lbs. Each

Documents / Support Tools

Video US 1	Available on Website
Video US 2	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com