



# Wera Ratchets

BE A TOOL REBEL



## Zyklop Metal Ratchet



### Small return angle

The fine 72 tooth ratchet mechanism has a low return angle of 5°. This short stroke allows fast and precise work in small spaces.



### Extremely slim Long leverage

Forged, chrome-molybdenum steel ratchet has no torque limitation and is designed to fit in tight areas.



### Secure socket lock mechanism

The ball lock holds sockets and attachments securely, ensuring safe operation. To release the socket simply press the release button.

Wera Metal Ratchets and Ratchet Sets			
Part Number	Description	Pcs/Pkg	Price
<a href="#">05004004055</a>	Wera Zyklop Metal ratchet, switch lever, 1/4 inch drive, 5 degree return angle, all metal construction, secure socket lock mechanism.	1	\$49.00
<a href="#">05004034055</a>	Wera Zyklop Metal ratchet, switch lever, 3/8 inch drive, 5 degree return angle, all metal construction, secure socket lock mechanism.	1	\$56.00
<a href="#">05004064055</a>	Wera Zyklop Metal ratchet, switch lever, 1/2 inch drive, 5 degree return angle, all metal construction, secure socket lock mechanism.	1	\$63.00



### Switch Lever

Switch lever for convenient change of direction.



# Zyklop Metal Ratchet and Socket Sets



## 3/8 inch Drive Imperial and Metric Ratchet Sets



3/8 inch Drive Metal Ratchet Sets		
Part Number	Description	Price
<b>05004051055</b>	Wera socket set with Zyklop Metal switch lever ratchet, 3/8 inch drive, SAE. 29 pieces. Durable cloth pouch included. Manufacturer part number 004051.	\$147.00
<b>05004048055</b>	Wera socket set with Zyklop Metal switch lever ratchet, 1/2 inch drive, metric. 28 pieces. Durable cloth pouch included. Manufacturer part number 004078.	\$147.00

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect.



Wera socket set with Zyklop Metal switch lever ratchet, 3/8 inch drive, SAE, 29 pieces. Includes the pieces listed in the table below.



Wera socket set with Zyklop Metal switch lever ratchet, 3/8 inch drive, metric, 29 pieces. Includes the pieces listed in the table below.

05004051055 Contents		
	3/8 Zyklop Metal ratchet	
	6-point socket	1/4 x 29, 5/16 x 29, 3/8 x 29, 7/16 x 29, 1/2 x 29, 9/16 x 29, 5/8 x 30, 11/16 x 30, 3/4 x 30
	Extension	3/8 x 200
	Wobble Extension	3/8 x 76
	Bit adaptor	3/8 x 1/4 x 44
	Hex-plus bit, 25mm long	5/32, 3/16, 7/32, 1/4, 5/16
	Phillips bit, 25mm long	PH1, PH2, PH3
	Posidriv® bit, 25mm long	PZ1, PZ2
	Torx® bit, 25mm long	TX 15, TX 20, TX 25, TX 27, TX 30, TX 40

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.

05004048055 Contents		
	3/8 Zyklop Metal ratchet	
	6-point socket	8 x 29, 10 x 29, 12 x 29, 13 x 29, 15 x 29, 16 x 30, 17 x 30, 18 x 30, 19 x 30
	Extension	3/8 x 200
	Wobble Extension	3/8 x 76
	Bit adaptor	3/8 x 1/4 x 44
	Hex-Plus bit, 25mm long	3, 4, 5, 6, 8
	Phillips bit, 25mm long	PH1, PH2, PH3
	Posidriv® bit, 25mm long	PZ1, PZ2
	Torx® bit, 25mm long	TX 15, TX 20, TX 25, TX 27, TX 30, TX 40

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.