



Wesco Industrial Products, Inc.

1250 Welsh Rd

North Wales, PA 19454

Phone: 800.445.5681 • Fax: 800.346.5511

Email: [info@wescomfg.com](mailto:info@wescomfg.com)

## PART NO. 261032, 3" X 30" FORK STRADDLE BASE POWERED STACKER



- 1-year warranty.
- Proven quality: Wesco® manufactured Hydraulic Cylinder.
- Battery and charger included.
- Forks lower to floor on all models.
- 5" Phenolic wheels on front, 4" swivel on rear
- 110V AC models available. (Special order, NO cancellations or returns.)
- To order add AC to the end of the battery powered stacker part #.

Example:

Battery Powered #261032

110V AC Powered #261032AC

- Meets ANSI B56.10 specifications.
- Power Drive option available.

[Video](#) | [Specifications](#) | [5th Wheel Steering Option](#) | [Stacker Low Profile Outrigger Option](#)

### Video



### Specifications



|                           |                          |
|---------------------------|--------------------------|
| <b>PART NUMBER</b>        | 261032                   |
| <b>MODEL</b>              | PESFL-64-30S             |
| <b>TYPE</b>               | Straddle Base Fork Model |
| <b>FRONT WHEEL</b>        | (2) 5" Phenolic          |
| <b>REAR SWIVEL CASTER</b> | (2) 4" Phenolic          |
| <b>LIFT HEIGHT</b>        | 64"                      |
| <b>CAPACITY</b>           | 1000 lb                  |
| <b>WIDTH FORKS</b>        | 3"                       |
| <b>LENGTH FORKS</b>       | 30"                      |
| <b>LOAD CENTER</b>        | 18"                      |
| <b>BASE LEG (ID/OD)</b>   | 25.5"/32"                |
| <b>OVERALL WIDTH</b>      | 32"                      |
| <b>OVERALL HEIGHT</b>     | 80"                      |
| <b>OVERALL DEPTH</b>      | 48"                      |
| <b>WEIGHT</b>             | 456 lb                   |

MADE IN THE USA




## 5th Wheel Steering Option

### 5TH WHEEL STEERING OPTION



5th Wheel Steering Option for easier mobility & precision steering in confined areas. Available only on 1,500 and 2,000 lb models. 8" locking polyurethane wheels. Spring loaded handle. Can be field installed. Order as separate option under Part # 261099

**Look**

**Stacker Low Profile Outrigger Option****STACKER LOW PROFILE OUTRIGGER OPTION**

Stacker Low Profile Outrigger Option