

# Enclosure Subpanels



## Subpanels for Two-Door Floor-Mount Enclosures

- Subpanels are fabricated from 10-gauge carbon steel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels are used in NEMA 12 double-door floor-mount enclosures and some double-door wall-mount enclosures



Shipping Schedule				
Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days
Color indicates shipping lead time in business days.				

Subpanels for Two-door Floor-Mount Enclosures					
Painted Steel	Price	Galvanized	Price	Nominal Enclosure Size HxW*	Subpanel Size AxB
<b><u>NPDD4242</u></b>	\$260.00	<b><u>NPDD4242G</u></b>	\$281.00	42 x 42	39.00 x 39.00 [991 x 991]
<b><u>NPDD4260</u></b>	\$381.00	<b><u>NPDD4260G</u></b>	\$381.00	42 x 60	38.00 x 56.00 [965 x 1422]
<b><u>NPDD4842</u></b>	\$294.00	<b><u>NPDD4842G</u></b>	\$294.00	48 x 42	45.00 x 39.00 [1143 x 991]
<b><u>NPDD4848</u></b>	\$352.00	<b><u>NPDD4848G</u></b>	\$352.00	48 x 48	44.00 x 44.00 [1118 x 1118]
<b><u>NPDD5442</u></b>	\$314.00	<b><u>NPDD5442G</u></b>	\$314.00	54 x 42	50.00 x 38.00 [1270 x 965]
<b><u>NPDD6048</u></b>	\$427.00	<b><u>NPDD6048G</u></b>	\$427.00	60 x 48	44.00 x 56.00 [1118 x 1422]
<b><u>NPDD6060</u></b>	\$527.00	<b><u>NPDD6060G</u></b>	\$527.00	60 x 60	56.00 x 56.00 [1422 x 1422]
<b><u>NPDD7260</u></b>	\$628.00	<b><u>NPDD7260G</u></b>	\$628.00	72 x 60	56.00 x 68.00 [1422 x 1727]
<b><u>NPDD7272</u></b>	\$750.00	—	—	72 x 72	68.00 x 68.00 [1727 x 1727]

Notes: Dimensions in inches [millimeters].  
 Letters in table correspond to letters on dimensional drawing.  
 \*Some floor-mount enclosures may be up to 2 in [51 mm] taller than height listed in this table.  
 Disconnect enclosures will be up to 2 in [51 mm] wider than width dimensions listed in this table.

## Dimensions

