


# 400, 800, 2300 & 2300D SERIES™ RACEWAYS

## Ordering Information


### Reducing Connector



**PART NUMBERS:**  
**2389A** (Ivory)  
**2389A-WH** (White)

For transitioning from 2300 Series Raceway to 400 Series Raceway.


### Radiused Divided Internal Elbow



**PART NUMBERS:**  
**2317DFO** (Ivory)  
**2317DFO-WH** (White)

A 90° internal corner with integral dividers provide 2" [51mm] cable bend radius for UTP and fiber optic installations.


### Radiused Divided Entrance End Fitting



**PART NUMBERS:**  
**2310DFO** (Ivory)  
**2310DFO-WH** (White)

Divided fitting to feed 2300 and 2300 Divided Series Raceway. Includes 1/2", 3/4", and 1" trade size KOs on back and top.


### Radiused Divided External Elbow



**PART NUMBERS:**  
**2318DFO** (Ivory)  
**2318DFO-WH** (White)

A 90° external corner with integral dividers provide 2" [51mm] cable bend radius for UTP and fiber optic installations.

### Radiused Divided Flat Elbow




**PART NUMBERS:**  
**2311DFO** (Ivory)  
**2311DFO-WH** (White)

A 90° flat corner with integral dividers provide 2" [51mm] cable bend radius for UTP and fiber optic installations.

## 400/800/2300/2300D Series Raceway Device Box Ordering Information


### Blank Cover



**PART NUMBERS:**  
**2336** (Ivory)  
**2336-WH** (White)

Use with any nonmetallic round device box to convert into a junction box.


### Fixture Box



**PART NUMBERS:**  
**2338A** (Ivory)  
**2338A-WH** (White)

For hanging fixtures, smoke/fire alarms and other security devices with 3 1/2" [89mm] or 4 1/16" [103mm] mounting centers. Has 1/2" trade size KO. Not for use with fans.


### Round Box Extension



**PART NUMBERS:**  
**2337A** (Ivory)  
**2337A-WH** (White)

For hanging fixtures, smoke/fire alarms and other security devices with 3 1/2" [89mm] or 4 1/16" [103mm] mounting centers. 5 1/2" [140mm] diameter with open base. Not for use with fans.

### Extra Deep Device Box



**PART NUMBERS:**  
**2344** (Ivory), **2344-WH** (White)  
**2344-2** (Ivory), **2344-2-WH** (White)

2344 one-gang, 2344-2 two-gang. Two-gang base has rectangular KO to enable extension from existing single-gang flush wallbox and 1/2" and 1" trade size concentric KOs. Accepts industry standard faceplates for switch and communication devices.

| CAT. NO.  | L              | W              | GANG |
|-----------|----------------|----------------|------|
| 2344      | 4 3/4" [121mm] | 4 3" [76mm]    | 1    |
| 2344-WH   | 4 3/4" [121mm] | 4 3" [76mm]    | 1    |
| 2344-2    | 4 3/4" [121mm] | 4 7/8" [124mm] | 2    |
| 2344-2-WH | 4 3/4" [121mm] | 4 7/8" [124mm] | 2    |