


PRO SERIES SERVICE FITTINGS

Compatible with Walkerdut Pro Series only


Walkerdut Pro Series Flush Brass Flanges Ordering Information (continued)

828SPTC Brass Duplex Cover Plate




Screw plugs. Screw plugs are 1 1/2" (38mm) in diameter.

829CK-1 Brass Communication Cover Plate




2 5/8" and 1" (67mm and 25mm) plugs.

829STC Brass Communication Cover Plate




Data slides. Feed through only, not for use with a mounting plate for communication jacks.

829CK-3/4 Brass Communication Cover Plate




2 5/8" and 3/4" (67mm and 19.1mm) plugs.

829CK Brass Communication Cover Plate



2 5/8" and 2 1/4" (67mm and 57mm) plugs.


829CK-1/2 Brass Communication Cover Plate



2 5/8" and 1/2" (67mm and 12.7mm) plugs.

NOTE: Brass covers and flanges are not interchangeable with aluminum or nonmetallic covers and flanges. Nonmetallic covers are interchangeable with aluminum flanges.

828DLR Brass Single Locking Receptacle Cover Plate




Single flip lid cover for 20A or 30A single locking receptacles. Device opening is 2 5/8" (67mm). For use with maximum female locking device of 1.58" diameter, and maximum male plug face of 2.25" diameter

SOURCE 1® SERVICE FITTINGS

Compatible with Walkerdut


Source 1 Series Service Fittings Ordering Information (continued)

S124B Carpet Flange




Flush brass carpet flange only with mounting screws.

829CK Cover Plate




Flush brass communication cover plate (2 5/8" and 2 1/4" diameter trade size screw plugs) with four mounting screws.

S125B Cover Plate




Flush brass power cover plate only (flip lid) with four mounting screws.

829CK-3/4 Cover Plate



Flush brass communication cover plate (2 5/8" and 3/4" diameter trade size screw plugs) with four mounting screws.

Cover Plate




PART NUMBERS:

S125BLK (Black)

S125BRN (Brown)


Nonmetallic double duplex membrane cover plate.

829CK-1 Cover Plate



Flush brass communication cover plate (2 5/8" and 1" diameter trade size screw plugs) with four mounting screws.

Cover Plate




PART NUMBERS:

S130BLK (Black)

S130BRN (Brown)


Nonmetallic double duplex membrane cover plate.

829CK-1/2 Cover Plate



Flush brass communication cover plate (2 5/8" and 1/2" diameter trade size screw plugs) with four mounting screws.

Cover Plate




PART NUMBERS:

829PSTC-BLK (Black)

829PSTC-BRN (Brown)


Flush polycarbonate communication cover plate with slides and four mounting screws.

828SPTC Cover Plate



Flush brass communication cover plate. 1 1/2" diameter trade size screw plugs.

829STC Cover Plate



Flush brass communication cover plate with slides and four mounting screws.