


RATCHET-PRO™ SERIES FLOOR BOXES

Ratchet-Pro Series Floor Box Cover Plate Ordering Information

Brass/Brushed Aluminum Duplex Cover Plate




PART NUMBERS:

895 (Brass)

895TCAL (Brushed Aluminum)

With flip lids, 5 1/2" (140mm) diameter for carpet.


896 Brass Communication or Power Cover Plate



With 2 5/8" (67mm) threaded opening, 5 1/2" (140mm) diameter for carpet.

NOTE: Sold without abandon plug.

Brass/Brushed Aluminum Duplex Cover Plate




PART NUMBERS:

895T (Brass)

895TAL (Brushed Aluminum)

With flip lids, 4 1/4" (105mm) diameter for tile.


896T Brass Communication or Power Cover Plate



With 2 5/8" (67mm) threaded opening, 4 1/4" (108mm) diameter for tile.

NOTE: Sold without abandon plug.

Brass/Brushed Aluminum Cover Plate



PART NUMBERS:


895SP (Brass)

895SPCAL (Brushed Aluminum)

With two screw plug openings, 5 1/2" [140mm] diameter for carpet.


NOTE: Screw plug openings are 1 1/2" (38mm) - 16 tapped openings.

896CK Brass Communication or Power Cover Plate



With 2 1/4" (57mm) threaded opening, 5 1/2" (140mm) diameter for carpet.


895TSP Brass Cover Plate



With two screw plug openings, 4 1/4" (108mm) diameter for tile.


NOTE: Screw plug openings are 1 1/2" (38mm) - 16 tapped openings.

896TCK Brass Communication or Power Cover Plate



With 2 1/4" (57mm) threaded opening, 4 1/4" (108mm) diameter for tile.

Brass/Brushed Aluminum GFI Receptacle Cover Plate




PART NUMBERS:

895GFI (Brass)

895GFICAL (Brushed Aluminum)

5 1/2" (140mm) diameter for carpet.

Brass/Brushed Aluminum Cover Plate




PART NUMBERS:

896CK-1/2 (Brass)

896CKAL-1/2 (Brushed Aluminum)

With 1/2" (12.7mm) threaded opening, 5 1/2" (140mm) diameter for carpet.

Brass/Brushed Aluminum GFI Receptacle Cover Plate




PART NUMBERS:

895TGFI (Brass)

895TGFIAL (Brushed Aluminum)

4 1/4" (108mm) diameter for tile.

Brass/Brushed Aluminum Cover Plate



PART NUMBERS:

896TCK-1/2 (Brass)

896TCKAL-1/2 (Brushed Aluminum)

With 1/2" (12.7mm) threaded opening, 4 1/4" (108mm) diameter for tile.

NOTE: All cover plates are furnished with gasket and three screws.
The 895P Polycarbonate Series Cover Plates must be field modified for dual service.