


ALA4800 SERIES™ RACEWAY


ALA4800 Series Raceway Ordering Information

ALA4800B-10 Dual Compartment Raceway Base




6063-T5 extruded aluminum, satin anodized finish, .078" (1.98mm) wall thickness. Base has integral divider for separation of service. Packed 40' (12m) per carton.

ALA4810B Blank End Fitting




For covering ends of raceway.

ALAC-5 Raceway Cover




6063-T5 extruded aluminum, satin anodized finish, .078" (1.98mm) wall thickness. Two covers per base. Allows only one compartment to be accessed at a time. Packed 40' (12m) per carton. ALAC-5 is compatible with ALA4800 Series and ALA3800 Series Raceways.

ALA4810B2 Entrance End Fitting




For feeding raceway, has two concentric 1/2" and 3/4" trade size KOs.

ALAWC Wire Clip




For holding conductors in place in long raceway runs. Snaps into grooves in base.

ALA4811 Flat Elbow




Makes 90° flat turn in a raceway run. Includes four ALA01 Couplings.

ALA01 Couplings




Joins lengths of inline ALA4800B-10 Raceway Base together. Two required per section of base.

ALA4815 Tee




For branch connections of two runs of ALA4800 Series Raceway. Includes six ALA01 Couplings.

ALA4806 Cover Clip




Stainless steel clip to cover joint where lengths of cover or base come together.

ALA4817 Internal Elbow




To make an internal turn in a raceway run. Includes four ALA01 Couplings.

ALA09 Grounding Adapter



For connection of equipment grounding conductor to provide additional ground to raceway.

ALA17A Internal Corner Coupling




For butting two raceway sections to form an internal 90° turn in a raceway run.

NOTE: These parts are compatible with both ALA4800 and ALA3800 Series Raceways.

ALA4800 SERIES RACEWAY


Ordering Information

ALA4810B2 Entrance End Cap




For feeding raceway. Has two concentric 1/2" and 3/4" knockouts.

ALA4817 Internal Mitered Elbow with Coupling




Makes 90° internal turns in runs of ALA4800 Series Raceway. Includes two (2) sets of two (2) ALA01 Couplings.

ALA4811 90° Flat Mitered Elbow with Coupling




Makes 90° turns in runs of ALA4800 Series Raceway. Includes two (2) sets of two (2) ALA01 Couplings.

ALA4817N Inverted Internal Mitered Elbow with Coupling




For connecting a vertical run of ALA4800 Series Raceway with a horizontal run of ALA4800 Series Raceway with its cover facing up. Includes four (4) ALA01 Couplings.

ALA4812A 45° Internal Mitered Elbow with Coupling




Makes 45° internal turns in runs of ALA4800 Series Raceway. Includes two (2) sets of two (2) ALA01 Couplings.

ALA4818 External Mitered Elbow with Coupling




Makes 90° external turns in runs of ALA4800 Series Raceway. Includes four (4) ALA01 Couplings.

ALA4812B 45° External Mitered Elbow with Coupling




Makes 45° external turns in runs of ALA4800 Series Raceway. Includes two (2) sets of two (2) ALA01 Couplings.

ALA11R 12" (51mm) Bend Radius Control Insert for Flat Elbow




Installs in ALA3811 Flat Elbow. For new and retrofit applications whether the cable installation is lay-in or pull-through.

ALA4815 Flat Tee with Coupling



Makes branch connections of two runs of ALA4800 Series Raceway. Includes three (3) sets of two (2) ALA01 Couplings.

ALA17/18R 12" (51mm) Bend Radius Control Insert for Internal & External Elbows



Inserts into ALA3817, ALA3817N, and ALA3818 fittings. For new and retrofit applications whether the cable installation is lay-in or pull-through.