



Industrial Control Transformer 1KVA 240,347,380 - 120X240 F2

By Acme Electric
Catalog # [CE1000N012CF2](#)

ICT 1KVA 240,347,380 - 120X240 F2



Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

Application

Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits.The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

Specifications

Certified Listed

- UL Listed

- cUL Listed

Current

Primary Voltage240, 347, 380 V
Secondary Voltage120 X 240 V

Dimensions

Weight29.8 lb.
Height6.9 in
Width7 in
Length6.23 in
Dimensions6.23 in x 7 in x 6.9 in

General

ColorBlack
UPC047503015933

Logistics

Pallet Quantity24
Carton Quantity1

Product Assets

[Catalog \[English\]](#)