

Scan the QR code  
to Watch installation  
instructions



# Encapsulated Transformers for Hazardous Locations

## CLASS I, DIV. 2

These transformers are for use in areas which may contain dangerous and corrosive, explosive or combustible gasses, liquids, or dusts due to accidental rupture or breakdown of their storage systems.

Petrochemical and industrial facilities may have atmospheres unsuitable for application of general purpose transformer.

### FEATURES

- Slotted mounting holes for quick and easy mounting
- Lifting hooks on single phase above 5 kVA three phase 3-9 kVA
- Wall mount design through 25 kVA single phase, through 15 kVA three phase
- Meet or exceeds NEMA, ANSI and UL standards
- Standard 10-Year Warranty

### APPLICATIONS

- Oil & Gas
- Petrochemical
- Mining
- Pulp & Paper
- Oil & Gas
- Marine
- Wastewater
- Industrial

### SPECIFICATIONS

- Class 1 Div. 2, Groups A, B, C, D
- Single Phase: 1 – 25 kVA
- Three Phase: 3 – 75 kVA
- 60 Hz
- 115°C Rise, 180°C Insulation System
- Meets T3C Temperature Classification
- 40°C Ambient
- NEMA 3R steel with ASA-61 gray powder coat finish



T1025K0220CSH



T1105K0220CSH



T3003K0011CSH



T3015K0011CSH