



Industrial Control Transformer

.250KVA 550/575/600 -110/115/120

F4

By Acme Electric
Catalog # [TB250N017F4](#)



ICT .250KVA 550/575/600 -110/115/120 F4

Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

Application

Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

General

Catalog Number	TB250N017F4
Color	Black
Secondary Voltage	110/115/120 V
UPC	047503013304

kVA	.250
-----	------

Dimensions

Dimensions	4.47 in x 4.5 in x 5.29 in
Height	5.29 in
Length	4.47 in
Weight	10 lb
Width	4.5 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	550/575/600 V

Certifications And Compliance

Certified Listed	• UL Listed • cUL Listed
------------------	--

Logistics

Carton Quantity	1
Pallet Quantity	48

Product Assets

[Brochures - Industrial Control Transformer](#)
[Catalogs - Acme Electric Catalog - Section 5 - Industrial Control Transformers](#)
[Specifications - TB250N017F4](#)



A Hubbell brand