



Industrial Control Transformer .750KVA 230,460,575 - 95,115 F3

By Acme Electric
Catalog # [TB750N011F3](#)

ICT .750KVA 230,460,575 - 95,115 F3

Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

Application

Acme's CE Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

Specifications

Certified Listed

- UL Listed



- cUL Listed

Current

Frequency Rating	50/60 Hz
Primary Voltage	230/460/575 V
Secondary Voltage	95, 115 V

Dimensions

Weight	28.1 lb.
Height	5.91 in
Width	5.25 in
Length	7 in
Dimensions	7 in x 5.25 in x 5.91 in

General

Color	Black
UPC	047503018330

Logistics

Pallet Quantity	48
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)