

SHS, LHS & IHS Crane Scales

Bringing strength and safety to the forefront of industrial settings



Features

- Bright LED display for easy viewing in most environments
- Rotating hook allows easy access while loading, then safely locks in place during weighing
- Rugged construction stands up to industrial use
- IHS's solid metal housing resists spills and protects internal components
- Remote control allows safe, hands-free operation
- Programmable auto power-off to save energy
- Rechargeable battery included for operation almost anywhere
- External calibration allows for verification and adjustment with weights
- Hold function on SHS and LHS models freezes the displayed weight, allowing time to elapse without losing the result
- Zero-tracking feature ensures display returns to zero reading
- AC adapter included

General Specifications

- Weighing units: kg, lb
- Power supply (SHS): 8.4VDC 800mA adapter, 4 x AA batteries, Internal rechargeable battery
- Power supply (LHS): 6VDC 600mA adapter, Internal rechargeable battery
- Power supply (IHS): 7.2VDC 2A adapter, Internal rechargeable battery
- Display (SHS): LED with 0.6" / 15mm-high digits
- Display (LHS): LED with 1" / 25mm-high digits
- Display (IHS): LED with 1.2" / 30mm-high digits
- Calibration: External
- Housing (SHS and IHS): Polycarbonate
- Housing (IHS): Die-cast aluminum
- Operating temperature: 0° to 40°C / 32° to 104°F

Applications

- Weighing
- Display hold



Remote Included
(2 x AAA Batteries)

WARRANTY
12
MONTHS

SHS Details

Model	Capacity	Readability	Shipping Weight	Shipping Dimensions	Price
SHS 100a	100lb / 50kg	0.02lb / 0.01kg	6lb / 2.72kg	12"x25"x10" / 305x635x254mm	\$495.00
SHS 300a	300lb / 150kg	0.05lb / 0.02kg	6lb / 2.72kg	12"x25"x10" / 305x635x254mm	\$505.00
SHS 600a	600lb / 300kg	0.1lb / 0.05kg	6lb / 2.72kg	12"x25"x10" / 305x635x254mm	\$515.00

LHS Details

Model	Capacity	Readability	Shipping Weight	Shipping Dimensions	Price
LHS 1000a	1000lb / 500kg	0.2lb / 0.1kg	13lb / 5.9kg	14"x18"x7" / 356x457x178mm	\$695.00
LHS 3000a	3000lb / 1500kg	0.5lb / 0.2kg	13lb / 5.9kg	14"x18"x7" / 356x457x178mm	\$795.00
LHS 4000a	4000lb / 2000kg	1lb / 0.5kg	13lb / 5.9kg	14"x18"x7" / 356x457x178mm	\$995.00

IHS Details

Model	Capacity	Readability	Shipping Weight	Shipping Dimensions	Price
IHS 2a	2000lb / 1000kg	0.5lb / 0.2kg	31lb / 14kg	16"x19"x11" / 406x483x279mm	\$1275.00
IHS 6a	6000lb / 3000kg	1lb / 0.5kg	34lb / 15.4kg	16"x19"x11" / 406x483x279mm	\$1375.00
IHS 10a	10000lb / 5000kg	2lb / 1kg	44lb / 20kg	16"x19"x11" / 406x483x279mm	\$1575.00
IHS 20a	20000lb / 10000kg	5lb / 2kg	70lb / 31.8kg	18"x21"x12" / 457x533x305mm	\$2275.00

Accessories

Item number	Description	Price
700660288	Calibration certificate.....	\$125.00

Adam Equipment, its directors, staff, owners and affiliated companies and organizations cannot be held liable for any resulting damage or injury sustained as a result of the machines being used in excess of their capacities and ultimate overload limits.